

SAC-3P- 7,0-PUO/A OD - Sensor/actuator cable



1426494

<https://www.phoenixcontact.com/us/products/1426494>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black RAL 9005, free cable end, on Valve connector A, cable length: 7 m, for outdoor applications

Commercial data

Item number	1426494
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1DAA
GTIN	4055626461229
Weight per piece (including packing)	333.5 g
Weight per piece (excluding packing)	325.85 g
Customs tariff number	85444290
Country of origin	PL

SAC-3P- 7,0-PUO/A OD - Sensor/actuator cable



1426494

<https://www.phoenixcontact.com/us/products/1426494>

Technical data

Product properties

Number of positions	3
---------------------	---

Electrical properties

Nominal voltage U_N	24 V DC
-----------------------	---------

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Valve connector A
------	-------------------

Cable/line

Cable length	7 m
--------------	-----

PUR halogen-free black [PUO]

Dimensional drawing	
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUO]
Conductor structure signal line	16x 0.20 mm
AWG signal line	20
Conductor cross-section	3x 0.5 mm ²
Wire diameter incl. insulation	2 mm ±0.05 mm
External cable diameter	5.90 mm ±0.1 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PP
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	≤ 40.1 Ω/km
Insulation resistance	70 GΩ*km
Nominal voltage, cable	300 V

SAC-3P- 7,0-PUO/A OD - Sensor/actuator cable



1426494

<https://www.phoenixcontact.com/us/products/1426494>

Test voltage Core/Core	3000 V (Spark test)
Minimum bending radius, fixed installation	10 x D
Minimum bending radius, flexible installation	15 x D
Smallest bending radius, fixed installation	59 mm
Smallest bending radius, movable installation	89 mm
Halogen-free	in accordance with DIN VDE 0472 part 815
	in accordance with EN 50267-2-1
Resistance to oil	According to DIN EN 50306
	According to DIN EN 60811-2-1, 138 h at 100°C
Other resistance	UV resistant
	hydrolysis and microbe resistant
	Good resistance to aggressive media
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation)
	-15 °C ... 105 °C (Cable, flexible installation)

SAC-3P- 7,0-PUO/A OD - Sensor/actuator cable



1426494

<https://www.phoenixcontact.com/us/products/1426494>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

UNSPSC

UNSPSC 21.0	31251501
-------------	----------

SAC-3P- 7,0-PUO/A OD - Sensor/actuator cable



1426494

<https://www.phoenixcontact.com/us/products/1426494>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com