

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, TPE halogen-free, welding sputter-resistant, highly flexible, yellow, Plug straight M12, coding: A, on Socket straight M12, coding: A, cable length: 4 m

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1432051                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF03                           |
| Product key                          | AF1ICB                         |
| GTIN                                 | 4055626432328                  |
| Weight per piece (including packing) | 22.22 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Country of origin                    | US                             |

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard, U.S. cables |
| Number of positions  | 4                     |
| No. of cable outlets | 1                     |
| Shielded             | no                    |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR   |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, weld slag-resistant coating  |
| Outer sheath, material                 | TPE   |

### Electrical properties

|                       |                           |
|-----------------------|---------------------------|
| Insulation resistance | $\geq 10 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 250 V AC                  |
|                       | 250 V DC                  |
| Nominal current $I_N$ | 4 A                       |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.4 Nm (M12 connector) |
|-------------------|------------------------|

### Connector

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

## Connection 1

|                     |                   |
|---------------------|-------------------|
| Type                | Plug straight M12 |
| Number of positions | 4                 |
| Coding type         | A                 |

## Connection 2

|                     |                     |
|---------------------|---------------------|
| Type                | Socket straight M12 |
| Number of positions | 4                   |
| Coding type         | A                   |

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 4 m |
|--------------|-----|

TPE, highly flexible, yellow [652]

|   |   |
|---|---|
| Dimensional drawing                           |  |
| UL AWM Style                                  | 20327 (105 °C / 300 V)  |
| Number of positions                           | 4   |
| Shielded                                      | no  |
| Cable type                                    | TPE, highly flexible, yellow [652]  |
| Conductor structure signal line               | 19x 0.03 in.  |
| AWG signal line                               | 22  |
| Conductor cross-section                       | 4x 0.34 mm <sup>2</sup> (Signal line)   |
| Wire diameter incl. insulation                | 0.05 in. ±0.02 mm   |
| External cable diameter                       | 5.33 mm ±0.13 mm  |
| Outer sheath, material                        | TPE   |
| External sheath, color                        | yellow  |
| Conductor material                            | Bare Cu litz wires  |
| Material wire insulation                      | SRPVC   |
| Single wire, color                            | brown, white, blue, black   |
| Overall twist                                 | 4 wires, twisted  |
| Nominal voltage, cable                        | 300 V   |
| Test voltage                                  | Spark test  |
| Minimum bending radius, flexible installation | 8 x D   |
| Smallest bending radius, fixed installation   | 10 x D  |
| Smallest bending radius, movable installation | 43 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 8 x D                                |
| Dynamic load capacity (torsion)               | Torsion: ±360 °/m, Torsion cycles: 10000000   |

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

|                                 |   |
|---------------------------------|---|
| Halogen-free                    | yes   |
| Flame resistance                | in acc. with UL FT4                             |
| Other resistance                | oil resistant (to UL 2256)                      |
|                                 | welding sputter-resistant                       |
|                                 | sunlight resistant (720 h test per UL 2256)     |
| Ambient temperature (operation) | -5 °C ... 105 °C (Cable, flexible installation) |
|                                 | -30 °C ... 105 °C (cable, fixed installation)   |

## Environmental and real-life conditions

### Ambient conditions

|   |   |
|---|---|
| Degree of protection  | IP65  |
|   | IP67  |
|   | IP68  |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket)                |
| Ambient temperature (operation) (Cable, fixed installation)       | -30 °C ... 105 °C (cable, fixed installation)   |
| Ambient temperature (operation) (Cable, flexible installation)    | -5 °C ... 105 °C (Cable, flexible installation) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-101 |

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

## Drawings

Dimensional drawing



Plug, M12 x 1, straight

Dimensional drawing



M12 x 1 socket, straight

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable

1432051

<https://www.phoenixcontact.com/us/products/1432051>

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable

1432051

<https://www.phoenixcontact.com/us/products/1432051>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

# SAC-4P-M12MS/ 4,0-652/M12FS - Sensor/actuator cable



1432051

<https://www.phoenixcontact.com/us/products/1432051>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)