

SAC-6P-MR/ 0,5-970/FR SCO - Bus system cable



1425423

<https://www.phoenixcontact.com/us/products/1425423>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system cable, VARAN (100 Mbps), 6-position, SANTOPRENE halogen-free/TPE halogen-free, black RAL 9005, shielded, Plug angled M12 SPEEDCON, coding: A, on Socket angled M12 SPEEDCON, coding: A, cable length: 0.5 m

Commercial data

Item number	1425423
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1CMM
GTIN	4055626399041
Weight per piece (including packing)	75.7 g
Weight per piece (excluding packing)	75.7 g
Country of origin	PL

SAC-6P-MR/ 0,5-970/FR SCO - Bus system cable



1425423

<https://www.phoenixcontact.com/us/products/1425423>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	VARAN
Number of positions	6

Interfaces

Signal type/category	VARAN, 100 Mbps
----------------------	-----------------

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC
Transmission speed	100 Mbps

Connector

Connection 1

Type	Plug angled M12 SPEEDCON
Number of positions	6
Locking type	SPEEDCON
Coding type	A (Standard)

Connection 2

Type	Socket angled M12 SPEEDCON
Number of positions	6
Locking type	SPEEDCON
Coding type	A (Standard)

Cable/line

Cable length	0.5 m
--------------	-------

VARAN [970]

Dimensional drawing	
Cable weight	81 kg/km
Number of positions	6
Shielded	yes
Cable type	VARAN [970]

SAC-6P-MR/ 0,5-970/FR SCO - Bus system cable



1425423

<https://www.phoenixcontact.com/us/products/1425423>

Conductor structure	1x2xAWG22/19 + 1x4xAWG24/19
Conductor structure signal line	19x 0.13 mm
AWG signal line	24
Conductor structure, voltage supply	19x 0.16 mm
AWG power supply	22
Conductor cross-section	4x 0.25 mm ² (Signal line)
	2x 0.38 mm ² (Power supply)
Wire diameter incl. insulation	1.35 mm (Signal line)
	1.5 mm (Power supply)
External cable diameter	7.80 mm ±0.2 mm
Outer sheath, material	SANTOPRENE halogen-free
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material, filler	Yarn
Material wire insulation	PP
Single wire, color	brown, blue, white/orange, white/green, green, orange
Type of pair shielding	Tinned copper braided shield, 95 % covering
Overall twist	1 star quad and 2 wires with 2 fillers
Max. conductor resistance	77 Ω/m (Data cable)
Insulation resistance	5 GΩ*km (Data cable)
Wave impedance	100 Ω ±15 %
Working capacitance	50 nF (Data cable)
Nominal voltage, cable	125 V (Data cable)
	48 V (Power supply)
Test voltage	2000 V (Power supply)
	max. 700 V AC (Data cable)
Smallest bending radius, fixed installation	≥ 93 mm
Smallest bending radius, movable installation	≥ 93 mm
Dynamic load capacity (bending)	Max. bending cycles: 3000000, Bending radius: 93 mm, Traversing path: 2 m, Traversing rate: 1 m/s, Acceleration: 2 m/s ²
Halogen-free	in accordance with DIN EN 50267-2-1
Ambient temperature (operation)	-20 °C ... 80 °C (Cable)
Ambient temperature (installation)	0 °C ... 50 °C

SAC-6P-MR/ 0,5-970/FR SCO - Bus system cable



1425423

<https://www.phoenixcontact.com/us/products/1425423>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-6P-MR/ 0,5-970/FR SCO - Bus system cable



1425423

<https://www.phoenixcontact.com/us/products/1425423>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com