

# SACC-P12FS-4PL-CM M - Connector



1438151

<https://www.phoenixcontact.com/us/products/1438151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 4-position, unshielded, Socket straight M12 Push-Pull, coding: A, Push-lock spring connection, knurl material: Plastic, external cable diameter 4 mm ... 8 mm

## Your advantages

- Time-saving Push-Lock connection: Tool-free connection and disconnection of conductors by opening the contact levers
- Intuitive connection: Easy assignment of individual litz wires with color-coded and numerical identification of the contact levers
- Integrated Push-in Technology: Wire rigid and pretreated conductors easily by means of simple, direct insertion
- Shock- and vibration-resistant connection: Proven spring-cage technology guarantees secure and reliable contacting
- Save time, thanks to installation with push-pull fast locking

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1438151       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF33          |
| Product key                          | AF2CEA        |
| GTIN                                 | 4063151815912 |
| Weight per piece (including packing) | 23.6 g        |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-P12FS-4PL-CM M - Connector



1438151

<https://www.phoenixcontact.com/us/products/1438151>

## Technical data

### Notes

|               |                                                                                                                                                                                                                                         |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Mounting

|               |                                                                    |
|---------------|--------------------------------------------------------------------|
| Assembly note | The wires can be connected both with ferrules and without ferrules |
|---------------|--------------------------------------------------------------------|

### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Number of positions  | 4                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |

#### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

#### External dimensions

|                  |               |
|------------------|---------------|
| Outside diameter | 4 mm ... 8 mm |
|------------------|---------------|

### Material specifications

|                                        |         |
|----------------------------------------|---------|
| Flammability rating according to UL 94 | V0      |
| Seal material                          | NBR     |
| Material of grip body                  | PA 6.6  |
| Contact material                       | CuSn    |
| Contact surface material               | Ni/Au   |
| Contact carrier material               | PA 6.6  |
| Material for screw connection          | Plastic |

### Connection data

#### Conductor connection

|                              |                                                                 |
|------------------------------|-----------------------------------------------------------------|
| Connection method            | Push-lock spring connection                                     |
| Connection cross section     | 0.14 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (without ferrule) |
|                              | 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (with ferrule)     |
| Connection cross section AWG | 26 ... 18 (without ferrule)                                     |
|                              | 26 ... 20 (with ferrule)                                        |

# SACC-P12FS-4PL-CM M - Connector



1438151

<https://www.phoenixcontact.com/us/products/1438151>

|                                         |                                            |
|-----------------------------------------|--------------------------------------------|
| Stripping length of the individual wire | 7 mm                                       |
| Tightening torque                       | 0.4 Nm (Connector with coupling sleeve)    |
|                                         | 1.5 Nm (Pressure nut with coupling sleeve) |

## Connection assignment

|                                                           |        |
|-----------------------------------------------------------|--------|
| Contact   Color (signal designation)   Contact (optional) | 1 = BN |
|                                                           | 2 = WH |
|                                                           | 3 = BU |
|                                                           | 4 = BK |

## Electrical properties

|                       |                                                     |
|-----------------------|-----------------------------------------------------|
| Rated surge voltage   | 2.5 kV                                              |
| Contact resistance    | $\leq 5 \text{ m}\Omega$                            |
| Insulation resistance | $\geq 100 \text{ M}\Omega$                          |
| Nominal voltage $U_N$ | 250 V AC                                            |
|                       | 250 V DC                                            |
| Nominal current $I_N$ | 4 A (2 A when using $0.14 \text{ mm}^2$ conductors) |

## Mechanical properties

### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

## Connector

### Connection 1

|                   |           |
|-------------------|-----------|
| Head design       | Socket    |
| Head cable outlet | straight  |
| Head thread type  | M12       |
| Head locking type | Push-Pull |
| Coding            | A         |

## Cable/line

|                                         |           |
|-----------------------------------------|-----------|
| Signal type/category                    | Universal |
| Stripping length of the individual wire | 7 mm      |

## Environmental and real-life conditions

### Ambient conditions

|                                                                   |                                  |
|-------------------------------------------------------------------|----------------------------------|
| Degree of protection                                              | IP65                             |
|                                                                   | IP67                             |
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |

## Standards and regulations

### M12

|                      |               |
|----------------------|---------------|
| Standard designation | M12 connector |
|----------------------|---------------|

# SACC-P12FS-4PL-CM M - Connector



1438151

<https://www.phoenixcontact.com/us/products/1438151>

|                          |                 |
|--------------------------|-----------------|
| Standards/specifications | IEC 61076-2-101 |
| Standard designation     | M12-Push-Pull   |
| Standards/specifications | IEC 61076-2-010 |


# SACC-P12FS-4PL-CM M - Connector

1438151


<https://www.phoenixcontact.com/us/products/1438151>

## Drawings

Dimensional drawing



Functional drawing




Functional drawing

# SACC-P12FS-4PL-CM M - Connector

1438151

<https://www.phoenixcontact.com/us/products/1438151>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

# SACC-P12FS-4PL-CM M - Connector



1438151

<https://www.phoenixcontact.com/us/products/1438151>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-P12FS-4PL-CM M - Connector



1438151

<https://www.phoenixcontact.com/us/products/1438151>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)