

# SACC-DSI-M8FS-3CON-M10/1,5 - Device connector rear mounting



1425818

<https://www.phoenixcontact.com/us/products/1425818>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 3-position, Socket, M8, on free cable end, Individual wires, cable length: 1.5 m, 0.25 mm<sup>2</sup>, PVC litz wire

## Commercial data

Item number	1425818
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQIDB
GTIN	4055626428154
Weight per piece (including packing)	24.5 g
Weight per piece (excluding packing)	20.8 g
Customs tariff number	85444290
Country of origin	DE

# SACC-DSI-M8FS-3CON-M10/1,5 - Device connector rear mounting



1425818

<https://www.phoenixcontact.com/us/products/1425818>

## Technical data

### Mounting

Mounting type	Rear mounting (M10)
---------------	---------------------

### Product properties

Product type	Circular connectors (device side)
Number of positions	3
Thread type	M8

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Connection data

#### Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	0.25 mm <sup>2</sup>

### Connector

#### Connection 1

Head design	Socket
Head thread type	M8

#### Connection 2

Head design	free cable end
-------------	----------------

### Cable/line

Cable length	1.5 m
Cable type	PVC litz wire
Cable cross section	0.25 mm <sup>2</sup>


# SACC-DSI-M8FS-3CON-M10/1,5 - Device connector rear mounting

1425818

<https://www.phoenixcontact.com/us/products/1425818>

## Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

# SACC-DSI-M8FS-3CON-M10/1,5 - Device connector rear mounting





1425818

<https://www.phoenixcontact.com/us/products/1425818>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1425818>

 <b>cUL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	4 A	24	-

 <b>UL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	30 V	4 A	24	-

# SACC-DSI-M8FS-3CON-M10/1,5 - Device connector rear mounting



1425818

<https://www.phoenixcontact.com/us/products/1425818>

## Classifications

### ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

### ETIM

ETIM 10.0	EC003570
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSI-M8FS-3CON-M10/1,5 - Device connector rear mounting



1425818

<https://www.phoenixcontact.com/us/products/1425818>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b6383f37-10cb-4b77-ac10-27cc362c2738

### EF3.1 Climate Change

CO2e kg	1.081 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)