

HC-CME-DD42-M - Power connector



1425840

<https://www.phoenixcontact.com/us/products/1425840>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON connection system for applications in the control cabinet



Commercial data

Item number	1425840
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BF61
Product key	AF7ABZ
GTIN	4055626428796
Weight per piece (including packing)	31.98 g
Weight per piece (excluding packing)	25 g
Customs tariff number	85389099
Country of origin	CN

HC-CME-DD42-M - Power connector



1425840

<https://www.phoenixcontact.com/us/products/1425840>

Technical data

Mounting

Assembly note	Use within a control cabinet that is protected against unauthorized access is essential to ensure correct use. At the installation location in the control cabinet, the cable bundle to be connected must be properly installed and fitted with strain relief. As the pin connector pattern does not provide a leading protective conductor contact (PE), consistent grounding must be ensured by the control cabinet assembly.
---------------	---

Product properties

Product type	Contact insert with a fixed no. of positions
Application	Signal
Number of positions	42
Connection profile	42
Contact numbering	1 - 42
Number of connections per position	1
Contact material type	turned rolled

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Dimensions

Mechanical characteristics

Contact diameter	1.6 mm
------------------	--------

Connection data

Connection technology

Connection technology	Crimp connection
Number of connections per position	1

Conductor connection

Conductor cross-section	0.14 mm ² ... 2.5 mm ²
Connection cross section AWG	26 ... 14
Stripping length of the individual wire	8 mm (0.14 mm ² ... 1.5 mm ²) 6 mm (2.5 mm ²)

Electrical properties

Rated voltage (III/3)	250 V
Rated surge voltage	4 kV
Rated current	10 A

Material specifications

HC-CME-DD42-M - Power connector



1425840

<https://www.phoenixcontact.com/us/products/1425840>

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC
Standards/regulations	PC
	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--


HC-CME-DD42-M - Power connector

1425840

<https://www.phoenixcontact.com/us/products/1425840>


Drawings

Schematic diagram



Connector pin assignment, connection side


Diagram



Derating diagram turned contacts

1425840

<https://www.phoenixcontact.com/us/products/1425840>



Derating diagram rolled contacts

HC-CME-DD42-M - Power connector



1425840

<https://www.phoenixcontact.com/us/products/1425840>

Classifications

ECLASS

ECLASS-13.0

27440205

ETIM

ETIM 9.0

EC000438

UNSPSC

UNSPSC 21.0

39121500

HC-CME-DD42-M - Power connector



1425840

<https://www.phoenixcontact.com/us/products/1425840>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com