

SAC-3P-M 8MS/ 5,0-PVC - Sensor/actuator cable



1447277

<https://www.phoenixcontact.com/us/products/1447277>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, Plug straight M8, on free cable end

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1447277 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | AF1BBA |
| GTIN | 4046356661324 |
| Weight per piece (including packing) | 132.5 g |
| Weight per piece (excluding packing) | 114.224 g |
| Country of origin | DE |

SAC-3P-M 8MS/ 5,0-PVC - Sensor/actuator cable



1447277

<https://www.phoenixcontact.com/us/products/1447277>

Technical data

Product properties

| | |
|--------------|-----------------------|
| Product type | Sensor/actuator cable |
|--------------|-----------------------|

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |

Connector

Connection 1

| | |
|------|------------------|
| Type | Plug straight M8 |
|------|------------------|

Connection 2

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

SAC-3P-M 8MS/ 5,0-PVC - Sensor/actuator cable



1447277

<https://www.phoenixcontact.com/us/products/1447277>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

SAC-3P-M 8MS/ 5,0-PVC - Sensor/actuator cable



1447277

<https://www.phoenixcontact.com/us/products/1447277>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com