

# SACC-CI-M12MS-4CON-L90 SCO - Contact carrier



1436660

<https://www.phoenixcontact.com/us/products/1436660>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 4-position, Pin, angled, M12, A-coding, Wave soldering, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

## Commercial data

Item number	1436660
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AB23
Product key	ABQAHM
GTIN	4046356438735
Weight per piece (including packing)	4.99 g
Weight per piece (excluding packing)	3.2 g
Customs tariff number	85366990
Country of origin	DE

1436660

<https://www.phoenixcontact.com/us/products/1436660>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Signal
Number of positions	4
No. of control contacts	4
Seal present	yes
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Electrical properties

Rated surge voltage	2.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	250 V
Nominal current $I_N$	4 A

### Connection data

Connection method	Wave soldering
-------------------	----------------

### Signaling

Status display	no
Status display present	no

### Material specifications

Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM / EPDM
Flammability rating according to UL 94	V0

### Connector

# SACC-CI-M12MS-4CON-L90 SCO - Contact carrier



1436660

<https://www.phoenixcontact.com/us/products/1436660>

## Connection 1

Head design	Pin
Head cable outlet	angled
Head thread type	M12
Coding	A

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
	-40 °C ... 85 °C (without mechanical actuation)

## Standards and regulations


Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

## Packaging specifications

Type of packaging	Blister
-------------------	---------

## Drawings

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

# SACC-CI-M12MS-4CON-L90 SCO - Contact carrier



1436660

<https://www.phoenixcontact.com/us/products/1436660>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1436660>

 <b>cUL Recognized</b> Approval ID: E118976-20100522				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	4 A	22	-

 <b>UL Recognized</b> Approval ID: E118976-20100522				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	250 V	4 A	22	-

# SACC-CI-M12MS-4CON-L90 SCO - Contact carrier



1436660

<https://www.phoenixcontact.com/us/products/1436660>

## Classifications

### ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

### ETIM

ETIM 10.0	EC003557
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-CI-M12MS-4CON-L90 SCO - Contact carrier



1436660

<https://www.phoenixcontact.com/us/products/1436660>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)