

# SAC-3P- 3,0-534/A-1L-V 230V - Sensor/actuator cable



1453724

<https://www.phoenixcontact.com/us/products/1453724>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sensor/actuator cable, 3-position, PVC, black, free cable end, on Valve connector A, with 1 LED



## Commercial data

Item number	1453724
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1DAA
GTIN	4046356554695
Weight per piece (including packing)	165.8 g
Weight per piece (excluding packing)	159.8 g
Country of origin	PL

# SAC-3P- 3,0-534/A-1L-V 230V - Sensor/actuator cable



1453724

<https://www.phoenixcontact.com/us/products/1453724>

## Technical data

### Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Connection data

#### Conductor connection

Tightening torque	0.6 Nm
-------------------	--------

### Electrical properties

Nominal voltage $U_N$	230 V AC
	230 V DC
Nominal current $I_N$	4 A

### Connector

#### Connection 1


Type	free cable end
------	----------------

#### Connection 2

Type	Valve connector A
------	-------------------

### Cable/line

PVC, 0.75 mm<sup>2</sup>, black [534]

Dimensional drawing	
Cable weight	49.1 kg/km
Number of positions	3
Shielded	no
Cable type	PVC, 0.75 mm <sup>2</sup> , black [534]
Conductor structure signal line	24x 0.20 mm
AWG signal line	18
Conductor cross-section	3x 0.75 mm <sup>2</sup>

# SAC-3P- 3,0-534/A-1L-V 230V - Sensor/actuator cable



1453724

<https://www.phoenixcontact.com/us/products/1453724>

Wire diameter incl. insulation	1.7 mm ±0.1 mm
External cable diameter	5.30 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	26 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km (at 20 °C)
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	27 mm
Flame resistance	DIN VDE 0482
	DIN EN 50265-2-1
	in acc. to UL VW1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67

# SAC-3P- 3,0-534/A-1L-V 230V - Sensor/actuator cable





1453724

<https://www.phoenixcontact.com/us/products/1453724>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1453724>

 <b>CSA</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	230 V	4 A	-	-

 <b>CSAus</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	230 V	4 A	-	-

# SAC-3P- 3,0-534/A-1L-V 230V - Sensor/actuator cable



1453724

<https://www.phoenixcontact.com/us/products/1453724>

## Classifications

### ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	31251500
-------------	----------

# SAC-3P- 3,0-534/A-1L-V 230V - Sensor/actuator cable



1453724

<https://www.phoenixcontact.com/us/products/1453724>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	93fb062c-5a95-4584-9166-d8d3dc475f03

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)