

SACC-M8-SEAL - Sealing ring

1437070

<https://www.phoenixcontact.com/us/products/1437070>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Seal for M8 socket



Commercial data

Item number	1437070
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	ABQZCA
GTIN	4046356448222
Weight per piece (including packing)	0.058 g
Weight per piece (excluding packing)	0.058 g
Country of origin	DE

SACC-M8-SEAL - Sealing ring



1437070

<https://www.phoenixcontact.com/us/products/1437070>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Seal
Thread type	M8

SACC-M8-SEAL - Sealing ring



1437070

<https://www.phoenixcontact.com/us/products/1437070>

Classifications

ECLASS

ECLASS-13.0	27430319
ECLASS-15.0	27430319

ETIM

ETIM 10.0	EC001181
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-M8-SEAL - Sealing ring



1437070

<https://www.phoenixcontact.com/us/products/1437070>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com