

SAC-3P- 1,5-PUR/C-1L-Z LS - Sensor/actuator cable



1455272

<https://www.phoenixcontact.com/us/products/1455272>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Valve connector C (8 mm), with 1 LED, Wiring: Z diode, cable length: 1.5 m

Commercial data

Item number	1455272
Packing unit	1 pc
Minimum order quantity	25 pc
Product key	AF1DEA
GTIN	4046356573900
Weight per piece (including packing)	59.1 g
Weight per piece (excluding packing)	59.1 g
Country of origin	PL

SAC-3P- 1,5-PUR/C-1L-Z LS - Sensor/actuator cable



1455272

<https://www.phoenixcontact.com/us/products/1455272>

Technical data

Product properties

Product type	Sensor/actuator cable with valve connector
Number of positions	3

Electrical properties

Nominal voltage U_N	24 V AC
	24 V DC

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Valve connector C (8 mm)
Number of positions	3
Protective circuit	Z diode

Cable/line

Cable length	1.5 m
--------------	-------

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	30 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor cross-section	3x 0.5 mm ²
Wire diameter incl. insulation	1.5 mm ±0.05 mm (Signal line)
External cable diameter	4.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires

SAC-3P- 1,5-PUR/C-1L-Z LS - Sensor/actuator cable



1455272

<https://www.phoenixcontact.com/us/products/1455272>

Material wire insulation	PP
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 1200 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	22.5 mm
Smallest bending radius, movable installation	45 mm
Dynamic load capacity (bending)	Max. bending cycles: 15000000, Bending radius: 50 mm, Traversing path: 0.9 m, Traversing rate: 5 m/s, Acceleration: 30 m/s ²
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	according to DIN VDE 0482 According to DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	largely oil-resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (Cable, flexible installation)

SAC-3P- 1,5-PUR/C-1L-Z LS - Sensor/actuator cable



1455272

<https://www.phoenixcontact.com/us/products/1455272>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

1455272

<https://www.phoenixcontact.com/us/products/1455272>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com