

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting



1456080

<https://www.phoenixcontact.com/us/products/1456080>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 3-position, Socket, straight, M8, A-coding, on free cable end, Individual wires, cable length: 0.5 m, 0.25 mm², PVC litz wire

Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness
- Standard pin assignments and codings for signal transmission with a uniform design-in design

Commercial data

Item number	1456080
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQIDB
GTIN	4046356605908
Weight per piece (including packing)	12.9 g
Weight per piece (excluding packing)	9.7 g
Customs tariff number	85444290
Country of origin	DE

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting



1456080

<https://www.phoenixcontact.com/us/products/1456080>

Technical data

Mounting

Mounting type	Rear mounting (M10, with flat nut)
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Flammability rating according to UL 94	HB
Seal material	FKM
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR/PA 6.6
Conductor material	Tin-plated Cu litz wires

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A
Max. conductor resistance	80 Ω /km

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Socket

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting



1456080

<https://www.phoenixcontact.com/us/products/1456080>

Conductor cross-section	0.25 mm ²
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	0.5 m
Cable type	PVC litz wire
Wire diameter incl. insulation	1.5 mm ±0.1 mm
Single wire, color	brown, blue, black
Cable cross section	0.25 mm ²
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.20 mm
AWG signal line	24
Material wire insulation	PVC / UL
Thickness, insulation	0.21 mm
Nominal voltage, cable	450 V
Test voltage, cable	2500 V (Test duration: 1 minute)
Cable resistance	≥ 80 Ω/km
Cable insulation resistance	≥ 20 MΩ*km
Ambient temperature (operation)	-40 °C ... 105 °C (cable, fixed installation) -10 °C ... 105 °C

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Socket)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 105 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	-10 °C ... 105 °C

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting



1456080

<https://www.phoenixcontact.com/us/products/1456080>

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104


SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting

1456080

<https://www.phoenixcontact.com/us/products/1456080>

Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting





1456080

<https://www.phoenixcontact.com/us/products/1456080>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1456080>

 cUL Recognized Approval ID: E221474-20070307				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	4 A	24	-

 UL Recognized Approval ID: E221474-20070307				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	4 A	24	-

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting



1456080

<https://www.phoenixcontact.com/us/products/1456080>

Classifications

ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

ETIM

ETIM 10.0	EC003570
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M8FS-3CON-M10/0,5 - Device connector rear mounting



1456080

<https://www.phoenixcontact.com/us/products/1456080>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b13f2508-f05b-4466-807f-aa04cc202b68

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com