

AXL SE DI8/2 48 - Digital module

1438680

<https://www.phoenixcontact.com/us/products/1438680>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline Smart Elements, Digital input module, Digital inputs: 8 (floating), 48 V DC, connection technology: 2-conductor, degree of protection: IP20; The product is being prepared for compliance with the Cyber Resilience Act (CRA).

Product description

You can integrate Axioline Smart Elements into systems with the Smart Element interface. This Smart Element detects digital signals.

Your advantages

- 8 digital inputs in accordance with EN 61131-2 type 1 and type 3 for 48 V DC inputs
- Nominal voltage: 48 V DC
- Nominal current: 2.4 mA
- Connection of sensors in floating 2-conductor technology
- Filter time of < 1 ms
- Device rating plate stored



Commercial data

Item number	1438680
Packing unit	1 pc

AXL SE DI8/2 48 - Digital module

1438680

<https://www.phoenixcontact.com/us/products/1438680>



Minimum order quantity	1 pc
Sales key	DR05
Product key	DRIB31
GTIN	4063151816759
Weight per piece (including packing)	37.501 g
Weight per piece (excluding packing)	35 g
Customs tariff number	85389091
Country of origin	DE

AXL SE DI8/2 48 - Digital module




1438680

<https://www.phoenixcontact.com/us/products/1438680>

Technical data

Dimensions

Dimensional drawing		
Width		14.9 mm
Height		62.2 mm
Depth		62 mm

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Mounting

Mounting type	Plug-in mounting (Smart Element slot)
Mounting position	See the system in which the Smart Element is used.

Material specifications

Color (Housing)	gray (RAL 7042)
-----------------	-----------------

Interfaces

Smart Element interface	
Number of interfaces	1
Connection method	Card edge connector
Transmission speed	See system in which you use the Smart Element.
Start time until ready to operate	< 500 ms

System properties

Programming data (LocalbusSlave)	
Process data channel	8 bit
Input address area	1 Byte
Output address area	0 Byte
Fieldbus data telegram (PROFIBUS)	
Required parameter data	1 Byte
Required configuration data	6 Byte

Input data

Digital:

Input name	Digital inputs
Description of the input	EN 61131-2 types 1 and 3
Number of inputs	8 (floating)
Connection method	Push-in connection
Connection technology	2-conductor
Input voltage range	-60 V DC ... 60 V DC
Input voltage range "0" signal	-10 V DC ... 10 V DC
Input voltage range "1" signal	15 V DC ... 60 V DC
	-60 V DC ... -15 V DC
Nominal input voltage U_{IN}	48 V DC
Nominal input current at U_{IN}	± 2.4 mA
Current flow	linear until nominal current is reached, then constantly approx. 2.4 mA
Input filter time	< 1 ms
Process data update	typ. 330 μ s

Product properties

Product type	I/O component
Product family	Axioline Smart Elements
Type	modular
Mounting position	See the system in which the Smart Element is used.
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

Electrical properties

Maximum power dissipation for nominal condition	1.3 W
---	-------

Potentials: Communications power supply of the Smart Elements (U_{SE})

Supply voltage	using card edge connectors
----------------	----------------------------

Electrical isolation/isolation of the voltage ranges

Test voltage: Communications power supply / 24 V supply U_P	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply U_P / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: Communications supply / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O channel / supply logic	500 V AC, 50 Hz, 1 min
Test voltage: I/O channel / 24 V supply U_P	100 V AC, 50 Hz, 1 min
Test voltage: I/O channel / functional ground	500 V AC, 50 Hz, 1 min
Test voltage: I/O channel / I/O channel	100 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	I/O
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline Smart Elements" user manual.

I/O

Connection method	Push-in connection
Note on the connection method	Please observe the information provided on conductor cross-sections in the "Axioline Smart Elements" user manual.
Conductor cross-section, rigid	0.25 mm² ... 1.5 mm²
Conductor cross-section, flexible	0.25 mm² ... 1.5 mm²
Conductor cross-section AWG	24 ... 16
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm² ... 1.5 mm²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.25 mm² ... 1.5 mm²
	0.25 mm² ... 1.5 mm²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm² ... 1.5 mm²
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	30g
Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27	10g

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

AXL SE DI8/2 48 - Digital module


1438680

<https://www.phoenixcontact.com/us/products/1438680>




Drawings

Dimensional drawing



Dimensions

Connection diagram




Connection example

AXL SE DI8/2 48 - Digital module

1438680

<https://www.phoenixcontact.com/us/products/1438680>

Block diagram



Internal wiring of the terminal points

AXL SE DI8/2 48 - Digital module



1438680

<https://www.phoenixcontact.com/us/products/1438680>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1438680>



cULus Listed

Approval ID: E238705



cULus Listed

Approval ID: E238705

AXL SE DI8/2 48 - Digital module



1438680

<https://www.phoenixcontact.com/us/products/1438680>

Classifications

ECLASS

ECLASS-13.0	27242604
ECLASS-15.0	27242604

ETIM

ETIM 10.0	EC001599
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

1438680

<https://www.phoenixcontact.com/us/products/1438680>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com