

SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting



1440669

<https://www.phoenixcontact.com/us/products/1440669>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 flush-type socket, front mounting

Device connector rear mounting, 8-position, Socket, straight, M12-SPEEDCON, X-coding, Wave soldering, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1440669
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB23
Product key	ABQAIA
GTIN	4046356504591
Weight per piece (including packing)	11.225 g
Weight per piece (excluding packing)	9.736 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting



1440669

<https://www.phoenixcontact.com/us/products/1440669>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Mounting

Mounting type	Rear mounting (M12 x 1)
---------------	-------------------------

Product properties

Product type	Circular connectors (device side)
Number of positions	8
Shielded	no
Coding	X
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Contact carrier	PA 6.6
Material Contact	Cu alloy
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

Electrical properties

Contact resistance	< 5 mΩ
Insulation resistance	> 100 MΩ
Nominal voltage U_N	60 V
Nominal current I_N	0.5 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
-------------	--------

SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting



1440669

<https://www.phoenixcontact.com/us/products/1440669>

Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	X

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101


SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting



1440669

<https://www.phoenixcontact.com/us/products/1440669>

Drawings



M12 socket pin assignment, 8-pos, view of socket side

SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting





1440669

<https://www.phoenixcontact.com/us/products/1440669>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1440669>

 cUL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

 UL Recognized Approval ID: E335024-20120308				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting



1440669

<https://www.phoenixcontact.com/us/products/1440669>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-FS-8CON-L180-10G SCO - Device connector rear mounting



1440669

<https://www.phoenixcontact.com/us/products/1440669>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	1d0a11fa-3250-4374-b701-c98a3a83eb48

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com