

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 4-position, Socket straight M12, coding: A, Insulation displacement connection, knurl material: Stainless steel 1.4404, external cable diameter 3.5 mm ... 6 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1440766 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF31 |
| Product key | AF2CCA |
| GTIN | 4046356517027 |
| Weight per piece (including packing) | 16 g |
| Weight per piece (excluding packing) | 16.3 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

Technical data

Notes

| | |
|---------------|---|
| Assembly note | NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

Mounting

| | |
|---------------|---|
| Assembly note | AWG 20 conductor cross-section upon request |
|---------------|---|


Product properties

| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |
| Cable outlet | straight |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Dimensions

| | |
|------------------------|--|
| Dimensional drawing |  |
| Length | 51 mm |
| Wrench size, union nut | 13 mm |

External dimensions

| | |
|------------------|-----------------|
| Outside diameter | 3.5 mm ... 6 mm |
|------------------|-----------------|

Housing

| | |
|------------------|---------|
| Diameter housing | 16.3 mm |
|------------------|---------|

Material specifications

| | |
|--|-----------------|
| Flammability rating according to UL 94 | V0 |
| Seal material | Neoprene FKM |
| Material of grip body | PA 6 |
| Contact material | CuSn |

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

| | |
|-------------------------------|------------------------|
| Contact surface material | Ni/Au |
| Contact carrier material | TPU |
| Material for screw connection | Stainless steel 1.4404 |
| Wire insulation material | PVC / PE / PP / rubber |

Connection data

Conductor connection

| | |
|------------------------------|---|
| Connection method | Insulation displacement connection |
| Connection cross section | 0.14 mm ² ... 0.34 mm ² |
| Connection cross section AWG | 26 ... 22 |
| Tightening torque | 0.4 Nm (M12 knurl) 1.2 Nm (Pressure nut) |

Connection assignment

| | |
|---|--------|
| Contact Color (signal designation) Contact (optional) | 1 = BN |
| | 2 = WH |
| | 3 = BU |
| | 4 = BK |

Electrical properties

| | |
|--------------------------------|----------------------|
| Rated surge voltage | 2.5 kV |
| Contact resistance | ≤ 5 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 125 V AC 125 V DC |
| Nominal current I _N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | A |

Cable/line

| | |
|-------------------------|-----------------|
| Signal type/category | Universal |
| External cable diameter | 3.5 mm ... 6 mm |

Environmental and real-life conditions

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

Ambient conditions

| | |
|---|-----------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 80 °C (Plug / socket) |
| Ambient temperature (assembly) | -5 °C ... 50 °C (During assembly) |

Standards and regulations

M12

| | |
|--------------------------|------------------------------|
| Standard designation | M12 connector |
| Standards/specifications | according to IEC 61076-2-101 |


SACC-M12FS-4QO-0,34-VA - Connector

1440766


<https://www.phoenixcontact.com/us/products/1440766>

Drawings

Dimensional drawing



M12 socket, straight,
QUICKON connection: 0.14 mm² ... 0.34 mm²



SACC-M12FS-4QO-0,34-VA - Connector

1440766

<https://www.phoenixcontact.com/us/products/1440766>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1440766>

DNV

Approval ID: TAE00002K4

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-M12FS-4QO-0,34-VA - Connector



1440766

<https://www.phoenixcontact.com/us/products/1440766>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.761 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com