

# FL MGUARD 4102 PCI - Router



1441187

<https://www.phoenixcontact.com/us/products/1441187>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Security-Router series, 2 RJ45 ports 10/100/1000 Mbps, degree of protection: IP00, Ambient temperature (operation): -20 °C ... 70 °C, NAT, VPN, Product certified in accordance with IEC 62443-4-2, Configurable stateful inspection firewall with full scope of functions

## Your advantages

- Central management tool
- Maximum security
- Maximum performance
- Integration of IT and OT security
- mGuard security technology

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1441187       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN30          |
| Product key                          | DNN332        |
| GTIN                                 | 4063151821456 |
| Weight per piece (including packing) | 153 g         |
| Weight per piece (excluding packing) | 89.78 g       |
| Customs tariff number                | 85176200      |
| Country of origin                    | DE            |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Material specifications

|                 |                             |
|-----------------|-----------------------------|
| Color (Housing) | Steel/stainless steel color |
|-----------------|-----------------------------|

### Interfaces

#### Ethernet

|                      |  |
|----------------------|--|
| Connection method    | RJ45   |
| Transmission speed   | 10/100/1000 Mbps                               |
| Transmission physics | Ethernet in RJ45 twisted pair                  |
| Transmission length  | 100 m (per segment)                            |
| Signal LEDs          | WAN link, WAN activity, LAN link, LAN activity |
| No. of channels      | 2 (RJ45 ports)                                 |

### System properties

#### Functionality

|                 |  |
|-----------------|--|
| Basic functions | Router with intelligent firewall and VPN for 250 tunnels |
|-----------------|--|

#### System requirements

|                    |                        |
|--------------------|------------------------|
| Supported browsers | HTTPS support required |
|--------------------|------------------------|

### Product properties

|                    |  |
|--------------------|--|
| Product type       | Security routers without DIN rail mounting         |
| Product family     | Security-Router                                    |
| Special properties | NAT  |
|                    | VPN  |
|                    | Product certified in accordance with IEC 62443-4-2 |
| Format             | PCI  |

#### Insulation characteristics

|                  |                                       |
|------------------|---------------------------------------|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
|------------------|---------------------------------------|

### Electrical properties

|                   |  |
|-------------------|--|
| Power consumption | max. 2.88 W                            |
| Local diagnostics | One LED per port Activity LED red      |
|                   | One LED per port Link active Green LED |

#### Supply

|                         |             |
|-------------------------|-------------|
| Power supply connection | Via PCI bus |
|-------------------------|-------------|

## Environmental and real-life conditions

### Ambient conditions

|   |                               |
|---|-------------------------------|
| Degree of protection                    | IP00                          |
| Ambient temperature (operation)         | -20 °C ... 70 °C              |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C              |
| Permissible humidity (operation)        | 5 % ... 95 % (non-condensing) |

## Mounting

|               |                             |
|---------------|-----------------------------|
| Mounting type | Plug-in mounting (PCI slot) |
|---------------|-----------------------------|

## EMC data

|                                 |   |
|---------------------------------|---|
| Electromagnetic compatibility   | Conformance with EMC Directive 2014/30/EU   |
| Conformance with EMC directives | IEC 61000-6-2 IEC 61000-4-2 (ESD) 6 kV contact discharge, 8 kV air discharge                          |
|                                 | IEC 61000-6-2 IEC 61000-4-3 (immunity to radiated interference) 10 V/m (80 MHz ... 6000 MHz)          |
|                                 | IEC 61000-6-2 IEC 61000-4-4 (burst) 2 kV power line, 2 kV data line                                   |
|                                 | IEC 61000-6-2 IEC 61000-4-5 (surge) power line: 1 kV (line/earth), 0.5 kV (line/line), 1 kV data line |
|                                 | IEC 61000-6-2 IEC 61000-4-6 (immunity to conducted interference) 10 V (150 kHz ... 80 MHz)            |
| Noise immunity                  | EN 61000-6-2:2005   |

### Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

## Signaling

|                |                        |
|----------------|------------------------|
| Status display | Link/activity per port |
|----------------|------------------------|

1441187

<https://www.phoenixcontact.com/us/products/1441187>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1441187>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705

**Cybersecurity Certificate**  
Approval ID: 968 CSP 1029.00 25



**UL Recognized**  
Approval ID: E238705



**cUL Recognized**  
Approval ID: E238705

**Cybersecurity Certificate**  
Approval ID: 968 CSP 1029.00 25

# FL MGUARD 4102 PCI - Router



1441187

<https://www.phoenixcontact.com/us/products/1441187>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19170406 |
| ECLASS-15.0 | 19170406 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001478 |
|-----------|----------|

1441187

<https://www.phoenixcontact.com/us/products/1441187>

## Environmental product compliance

### EU RoHS

|   |        |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes    |
| Exemption                               | 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |   |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | 4,4'-isopropylidenediphenol(CAS: 80-05-7) |
|-------------------------------------|---|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)