

SAC-3P-100,0-116/0,75 - Cable reel



1457416

<https://www.phoenixcontact.com/us/products/1457416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Cable reel, PUR/PVC, black RAL 9005, 3-wire, color single wire: black 1, black 2, green/yellow, cable length: 100 m



Commercial data

Item number	1457416
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4046356617543
Weight per piece (including packing)	5,163 g
Weight per piece (excluding packing)	4,996 g
Customs tariff number	85444290
Country of origin	PL

SAC-3P-100,0-116/0,75 - Cable reel

1457416

<https://www.phoenixcontact.com/us/products/1457416>

Technical data

Product properties


Product type	Cable by the meter
Application	Valve connector
Number of positions	3
Shielded	no

Cable/line

Cable length	100 m
--------------	-------

PUR/PVC, 0.75 mm², black [116]

Dimensional drawing



Cable weight	53.4 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR/PVC, 0.75 mm ² , black [116]
Conductor structure signal line	24x 0.20 mm
AWG signal line	18
Conductor cross-section	3x 0.75 mm ²
Wire diameter incl. insulation	1.7 mm ±0.05 mm
External cable diameter	5.80 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	26 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	29 mm

SAC-3P-100,0-116/0,75 - Cable reel



1457416

<https://www.phoenixcontact.com/us/products/1457416>

Smallest bending radius, movable installation	58 mm
Dynamic load capacity (bending)	Max. bending cycles: 1000000, Traversing path: 10 m, Traversing rate: 2 m/s, Acceleration: 2.5 m/s ²
Flame resistance	DIN VDE 0482
	DIN EN 50265-2-1
	in acc. with UL FT-2
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Low adhesion
Special properties	flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-3P-100,0-116/0,75 - Cable reel



1457416

<https://www.phoenixcontact.com/us/products/1457416>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1457416>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00371

SAC-3P-100,0-116/0,75 - Cable reel



1457416

<https://www.phoenixcontact.com/us/products/1457416>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-100,0-116/0,75 - Cable reel



1457416

<https://www.phoenixcontact.com/us/products/1457416>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	13.495 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com