

# SAC-3P-100,0-534/0,75 - Cable reel



1457432

<https://www.phoenixcontact.com/us/products/1457432>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Cable reel, PVC, black, 3-wire, color single wire: black 1, black 2, green/yellow, cable length: 100 m



## Commercial data

Item number	1457432
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4046356617567
Weight per piece (including packing)	4,530 g
Weight per piece (excluding packing)	3,597 g
Customs tariff number	85444995
Country of origin	DE

# SAC-3P-100,0-534/0,75 - Cable reel

1457432

<https://www.phoenixcontact.com/us/products/1457432>

## Technical data

### Product properties


Product type	Cable by the meter
Application	Valve connector
Number of positions	3
Shielded	no

### Cable/line

Cable length	100 m
--------------	-------

PVC, 0.75 mm<sup>2</sup>, black [534]

Dimensional drawing



Cable weight	49.1 kg/km
Number of positions	3
Shielded	no
Cable type	PVC, 0.75 mm <sup>2</sup> , black [534]
Conductor structure signal line	24x 0.20 mm
AWG signal line	18
Conductor cross-section	3x 0.75 mm <sup>2</sup>
Wire diameter incl. insulation	1.7 mm ±0.1 mm
External cable diameter	5.30 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	26 Ω/km (at 20 °C)
Insulation resistance	min. 20 MΩ*km (at 20 °C)
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	27 mm
Flame resistance	DIN VDE 0482 DIN EN 50265-2-1

# SAC-3P-100,0-534/0,75 - Cable reel



1457432

<https://www.phoenixcontact.com/us/products/1457432>

	in acc. to UL VW1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

# SAC-3P-100,0-534/0,75 - Cable reel



1457432

<https://www.phoenixcontact.com/us/products/1457432>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1457432>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00371

# SAC-3P-100,0-534/0,75 - Cable reel



1457432

<https://www.phoenixcontact.com/us/products/1457432>

## Classifications

### ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

### ETIM

ETIM 10.0	EC003249
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-3P-100,0-534/0,75 - Cable reel



1457432

<https://www.phoenixcontact.com/us/products/1457432>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	40.131 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)