

PV-YC 6/1-0,12T-0,12D-S03-NA - Photovoltaic Y distributor



1463066

<https://www.phoenixcontact.com/us/products/1463066>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Photovoltaic Y distributor, Range of articles: SUNCLIX, color: black, rated current: 40 A

Product description

Photovoltaic Y distributor with free conductor ends, 6 mm² main conductor with 6 mm² outlet

Commercial data

Item number	1463066
Packing unit	10 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Product key	ABLBCX
GTIN	4046356864763
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

PV-YC 6/1-0,12T-0,12D-S03-NA - Photovoltaic Y distributor



1463066

<https://www.phoenixcontact.com/us/products/1463066>

Technical data

Product properties

Product type	Photovoltaic connectors
Product family	SUNCLIX

Insulation characteristics

Protection class	II
------------------	----

Electrical properties

Rated voltage (III/2)	1100 V
Rated surge voltage (III/2)	12 kV
Rated current	40 A

Material specifications

Color	black
Flammability rating according to UL 94	V0

Cable/line

Cable type	PV1-F cables
------------	--------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Standards and regulations

Connection in acc. with standard	DIN EN 50521 (in accordance with)
----------------------------------	-----------------------------------

PV-YC 6/1-0,12T-0,12D-S03-NA - Photovoltaic Y distributor



1463066

<https://www.phoenixcontact.com/us/products/1463066>

Classifications

ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

PV-YC 6/1-0,12T-0,12D-S03-NA - Photovoltaic Y distributor



1463066

<https://www.phoenixcontact.com/us/products/1463066>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com