


PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Single-channel, electronic device protection for 48 V DC loads. Nominal current adjustable from 1-6 A. With floating remote indication contact. Can be combined with CLIPLINE terminal blocks. For installation on DIN rails.

Your advantages

- Simple application setup due to bridging option to CLIPLINE complete terminal block system
- More space in the control cabinet: narrowest protection on just 6 mm width
- Flexible use and reduction of inventory due to adjustable amp values on each device for wide range of applications

Commercial data

Item number	1471917
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL10
Product key	CLA135
GTIN	4063151880552
Weight per piece (including packing)	33.66 g
Weight per piece (excluding packing)	27.24 g
Customs tariff number	85363010
Country of origin	DE

Technical data

Notes

General

Note	Repeated hard short circuits can reduce the melting integral of the integrated backup fuse.
	This device is not a switching device acc. to UL508
	Always connect the negative pole to terminal IN- to ensure the internal power supply. Return currents from the loads must not be fed back to the power supply via IN- of the circuit breaker.

Product properties

Product type	Device circuit breakers
Product family	PTCB
Type	DIN rail module, one-piece
Number of positions	1

Insulation characteristics

Protection class	III
Pollution degree	2

Electrical properties

General

Operating voltage	30 V DC ... 56 V DC
Rated voltage	48 V DC
Rated current I_N	20 A (Total current input)
	6 A (Rated current output)
Rated current I_N	1 / 2 / 3 / 4 / 5 / 6 A DC (adjustable)
Rated current (pre-adjusted)	4 A
Rated surge voltage	0.5 kV
Tripping method	E (electronic)
Feedback resistance	max. 60 V DC
Required backup fuse	Only required if I_{max} of the power supply > the short-circuit switching capacity. Integrated failsafe element.
Short-circuit switching capacity	300 A
Dielectric strength	max. 60 V DC (Load circuit)
Fuse	electronic
Efficiency	> 99 %
Closed circuit current I_0	typ. 10 mA
Power dissipation	typ. 0.5 W (No-load operation)
	< 2.3 W (Nominal operation)
Module initialization time	< 350 ms
Waiting time after switch off of a channel	5 s (at overload / short circuit)
Measuring tolerance I	± 15 %

PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

Temperature derating	12 A (Total current at 60°C)
	20 A (Total current at 30°C)
	6 A (Channel current at 60°C)
	4 A (Channel current at 30°C)
MTBF (IEC 61709, SN 29500)	18684603 h (at 25 °C with 21 % load)
	6612007 h (at 40°C with 34.25% load)
	1140836 h (at 30° C with 100 % load)
Voltage drop	0.3 V (at 6 A)
Fail-safe element	15 A DC
Contact switching type	without electrical isolation

Load circuit

Shutdown time	≤ 10 ms (For short circuit > 3.0 x I _N)
	≤ 50 ms (with overload >2.0 x I _N)
	≤ 1 s (with overload 1.5...2.0 x I _N)
	≤ 4 s (with overload 1.1...1.5 x I _N)
Undervoltage switch-off	≤ 28.5 V DC (active)
	≥ 29.5 V DC (inactive)
Overvoltage switch-off	≥ 56.5 V DC (active)
	≤ 55.5 V DC (inactive)
Max. capacitive load	10000 µF (Depending on the current setting and the available short-circuit current, e.g., 3 mF at 48 V DC and 0.1 ohm cable)

Indicator/remote signaling

Connection name	Remote indication circuit
Switching function	N/O contact
Operating voltage	0 V DC ... 56 V DC
Operating current	100 mA DC

Connection data

Main circuit IN+

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section rigid	0.2 mm² ... 4 mm²
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.2 mm² ... 2.5 mm²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.2 mm² ... 2.5 mm²

Main circuit IN-

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section rigid	0.2 mm² ... 4 mm²

PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.2 mm ² ... 2.5 mm ²

Main circuit OUT

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.2 mm ² ... 2.5 mm ²

Remote indication circuit

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 14
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.2 mm ² ... 2.5 mm ²

Signaling

Channel LED off	off (Channel switched off)
Channel LED yellow	lit (Channel switched on, channel load > 80%) flashing (Programming mode active)
Channel LED green	lit (Channel switched on)
Channel LED red	lit (Channel switched off, over- or undervoltage active) ON temporarily (Channel switched off, 5 s cool-down phase, overload or short-circuit release) flashing (Channel switched off, ready to be switched back on, overload or short-circuit release) flashing quickly (Channel switched off, external voltage at the output, possible installation error)
Channel LED red-yellow	flashing (Overtemperature)

Dimensions

Dimensional drawing	
Width	6.2 mm
Height	105.8 mm

PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

Depth	55.6 mm (incl. DIN rail 7.5 mm)
-------	---------------------------------

Material specifications

Color	gray (RAL 7042)
Material	PBT
	PBT
Flammability rating according to UL 94	V-0

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-30 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	≤ 3000 m up to 52 °C (amsl)
	≤ 4000 m up to 46 °C (amsl)
Humidity test	96 h, 95 % RH, 40 °C
Shock (operation)	30g (IEC 60068-2-27, Test Ea)
Vibration (operation)	10 Hz ... 59.6 Hz (Amplitude ±0.35 mm; in accordance with IEC 60068-2-6, Test Fc)
	59.6 Hz ... 150 Hz (Acceleration 5g; in accordance with IEC 60068-2-6, Test Fc)
	5 Hz ... 100 Hz (Resonance search 4g; resonance frequency 4g; 90 min in accordance with DNV GL Class B)

Approvals

UL approval

Identification	UL/C-UL Listed UL 508
	UL Recognized UL 2367

Standards and regulations

Standards/specifications	EN 61000-6-2
Note	EMC – Immunity for industrial areas
Standards/specifications	EN 61000-6-3
Note	EMC – Emission for residential, business and commercial properties and small operations
Standards/specifications	EN 60068-2-78
Note	Environmental influences – Moisture and heat, constant
Standards/specifications	EN 50178
Note	Equipping power installations with electronic equipment
Standards/specifications	EN 60068-2-6
Note	Environmental influences – Vibrations (sinusoidal)
Standards/specifications	EN 60068-2-27
Note	Environmental influences – Shocks
Standards/specifications	EN 60068-2-30
Note	Environmental influences – Part 2–30: Tests – Test Db: Damp

PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

	heat, cyclical
--	----------------

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

PTCB E1 48DC/1-6A NO - Electronic circuit breaker




1471917


<https://www.phoenixcontact.com/us/products/1471917>

Drawings

Dimensional drawing




Diagram




Total current of input and channel current of output

Diagram



Trigger characteristic in the DC range

Block diagram



PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1471917>



UL Listed

Approval ID: E123528



cUL Listed

Approval ID: E123528



UL Recognized

Approval ID: E317172

PTCB E1 48DC/1-6A NO - Electronic circuit breaker



1471917

<https://www.phoenixcontact.com/us/products/1471917>

Classifications

ECLASS

ECLASS-13.0	27140401
ECLASS-15.0	27140401

ETIM

ETIM 10.0	EC003538
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

EF3.1 Climate Change

CO2e kg	4.924 kg CO2e
---------	---------------