

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable



1476831

<https://www.phoenixcontact.com/us/products/1476831>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, shielded (Advanced Shielding Technology), Plug straight M12 Push Pull, coding: A, on Socket straight M12 Push Pull, coding: A, cable length: 3 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1476831       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF06          |
| Product key                          | AF1CIC        |
| GTIN                                 | 4063151889753 |
| Weight per piece (including packing) | 131.233 g     |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable



1476831

<https://www.phoenixcontact.com/us/products/1476831>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard              |
| Number of positions  | 3                     |
| No. of cable outlets | 1                     |
| Shielded             | yes                   |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | V0  |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Outer sheath, material                 | PUR   |
| Conductor material                     | Bare Cu litz wires                          |

### Electrical properties

|                           |                            |
|---------------------------|----------------------------|
| Insulation resistance     | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$     | 48 V AC                    |
|                           | 60 V DC                    |
| Nominal current $I_N$     | 4 A                        |
| Max. conductor resistance | 58 $\Omega/\text{km}$      |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
| Max. bending cycles         | 10000000   |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Connection technology

|                   |           |
|-------------------|-----------|
| Connection method | Push-Pull |
|-------------------|-----------|

#### Conductor connection

|                   |           |
|-------------------|-----------|
| Connection method | Push-Pull |
|-------------------|-----------|

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable



1476831

<https://www.phoenixcontact.com/us/products/1476831>

|                   |                          |
|-------------------|--------------------------|
| Tightening torque | M12 push-pull connectors |
|-------------------|--------------------------|

## Connector

### Connection 1

|                     |                             |
|---------------------|-----------------------------|
| Type                | Plug straight M12 Push Pull |
| Number of positions | 3                           |
| Locking type        | Push Pull                   |
| Coding type         | A                           |

### Connection 2

|                     |                               |
|---------------------|-------------------------------|
| Type                | Socket straight M12 Push Pull |
| Number of positions | 3                             |
| Locking type        | Push Pull                     |
| Coding type         | A                             |

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 3 m |
|--------------|-----|

### PUR halogen-free black [PUR]

|   |   |
|---|---|
| Cable weight                                  | 31 kg/km  |
| UL AWM Style                                  | 20549   |
| Number of positions                           | 3   |
| Shielded                                      | yes   |
| Cable type                                    | PUR halogen-free black [PUR]  |
| Conductor structure signal line               | 42x 0.10 mm   |
| AWG signal line                               | 22  |
| Conductor cross-section                       | 3x 0.34 mm <sup>2</sup> (Signal line)                               |
| Wire diameter incl. insulation                | 1.27 mm ±0.02 mm (Signal line)                                      |
| External cable diameter                       | 4.65 mm ±0.15 mm  |
| Outer sheath, material                        | PUR   |
| External sheath, color                        | black-gray RAL 7021   |
| Conductor material                            | Bare Cu litz wires  |
| Material wire insulation                      | PP  |
| Single wire, color                            | brown, blue, black  |
| Thickness, insulation                         | ≥ 0.21 mm (Core insulation)<br>approx. 0.50 mm (Outer cable sheath) |
| Overall twist                                 | 3 wires, twisted  |
| Optical shield covering                       | 80 %  |
| Max. conductor resistance                     | max. 58 Ω/km (at 20 °C)   |
| Insulation resistance                         | ≥ 100 GΩ*km (at 20 °C)  |
| Nominal voltage, cable                        | ≤ 300 V   |
| Test voltage                                  | ≥ 3000 V  |
| Smallest bending radius, fixed installation   | 23 mm   |
| Smallest bending radius, movable installation | 47 mm   |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 47 mm,               |

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable



1476831

<https://www.phoenixcontact.com/us/products/1476831>

|                                 |  |
|---------------------------------|--|
|                                 | Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>   |
| Dynamic load capacity (torsion) | Torsion: ±180 °/m, Torsion cycles: ≥2000000, Torsional frequency: 35 cycles/min.   |
| Halogen-free                    | in accordance with DIN VDE 0472 part 815   |
| Flame resistance                | in accordance with UL 758/1581 FT2<br>DIN EN 60332-2-2 (20 s)  |
| Resistance to oil               | in accordance with DIN EN 60811-2-1  |
| Other resistance                | Highly resistant to acids, alkaline solutions and solvents<br>hydrolysis and microbe resistant<br>partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) |
| Special properties              | Flexible cable conduit capable<br>Silicone-free<br>Free of substances which would hinder coating with paint or varnish   |
| Ambient temperature (operation) | -40 °C ... 80 °C (cable, fixed installation)<br>-25 °C ... 80 °C (Cable, flexible installation)  |

## Environmental and real-life conditions

### Ambient conditions

|                                 |   |
|---------------------------------|---|
| Degree of protection            | IP65<br>IP67  |
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket)<br>-40 °C ... 80 °C (cable, fixed installation)<br>-25 °C ... 80 °C (Cable, flexible installation) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12-Push-Pull   |
| Standards/specifications | IEC 61076-2-010 |

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable

1476831

<https://www.phoenixcontact.com/us/products/1476831>

## Drawings

Dimensional drawing



M12 push-pull plug, straight, shielded

Dimensional drawing



M12 push-pull female, straight, shielded

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable

1476831

<https://www.phoenixcontact.com/us/products/1476831>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Schematic diagram



Pin assignment M12 socket, 3-pos., A-coded, view female side

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable

1476831

<https://www.phoenixcontact.com/us/products/1476831>

Circuit diagram



Contact assignment of the M12 connector and the M12 socket

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable



1476831

<https://www.phoenixcontact.com/us/products/1476831>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# SAC-3P-P12MS/ 3,0-PUR/P12FS SH - Sensor/actuator cable



1476831

<https://www.phoenixcontact.com/us/products/1476831>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)