

UCS HS-HH 145-125 AL - Heatsink




1481698

<https://www.phoenixcontact.com/us/products/1481698>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Heatsink for housing series: UCS, type: Half shell, material: Aluminum, anodized, width: 94.8 mm, height: 114.8 mm, Milling of the housing half-shell is required.



Your advantages

- Heatsink solutions enable devices to be used in thermally demanding applications
- Optimal thermal path for reliable heat dissipation
- Custom-tailored to various hot spots
- Heatsink solutions can be used in a variety of housing sizes
- Made-to-fit system solutions with mounting materials

Commercial data

Item number	1481698
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC03
Product key	ACFCAG
GTIN	4063151900731
Weight per piece (including packing)	297.3 g
Weight per piece (excluding packing)	270 g
Customs tariff number	76169990
Country of origin	CN

Technical data

Notes

Assembly note	Milling of the housing half-shell is required.
General	Please observe the application note in the download area.
General	Individual milling possible.
Order information:	Mounting screws are supplied as standard.
Recommendation	Further information and detailed dimensions are available in the download area.

Product properties

Product type	Heatsink
Housing type	Heatsink
Housing type	Universal housings
Housing series	UCS
Ventilation openings present	no

Dimensions

Width	94.8 mm
Height	114.8 mm
Depth	28 mm

Material specifications

Color (Housing)	aluminum color
Material	Aluminum
Surface characteristics	anodized

Environmental and real-life conditions

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.15 mm (10 Hz ... 58.1 Hz)
Acceleration	2g (58.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	15g
Shock duration	11 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

UCS HS-HH 145-125 AL - Heatsink



1481698

<https://www.phoenixcontact.com/us/products/1481698>

Test for substances that would hinder coating with paint or varnish

Specification	VDMA 24364:2018-05
Result	Test passed

Ambient conditions

Max. IP code to attain	IP40
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C


Mounting

Mounting type	Screw mounting
Mounting position	any


Packaging specifications

Type of packaging	Box packaging
-------------------	---------------

Drawings



The thermal path in an electronics housing system




Power dissipation diagram for 0 K ... 100 K

UCS HS-HH 145-125 AL - Heatsink

1481698

<https://www.phoenixcontact.com/us/products/1481698>



Power dissipation diagram for 0 K ... 30 K

UCS HS-HH 145-125 AL - Heatsink

1481698

<https://www.phoenixcontact.com/us/products/1481698>



Classifications

ECLASS

ECLASS-13.0	27260501
ECLASS-15.0	27260501

UCS HS-HH 145-125 AL - Heatsink



1481698

<https://www.phoenixcontact.com/us/products/1481698>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com