

FOC-SJ:14-SJ:14-HB02/18,0PRG01 - FO patch cable



1500186

<https://www.phoenixcontact.com/us/products/1500186>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled FO cable, PROFINET cable type B, 200/230 µm PCF fiber, SC-RJ/IP67 push-pull metal housing on both sides, PVC outer sheath, halogen-free, ozone- and UV-resistant, in conduit, for fixed indoor installation, length: 13 m



Your advantages

- High degree of reliability, thanks to the exceptional quality
- Reliable even in EMC-sensitive applications
- Fast data transmission for demanding applications
- Flexible installation, thanks to PVC outer sheath
- Including individual test report
- Universal installation cables for fixed installation indoors and outdoors (direct underground installation not permitted)
- Additional line protection thanks to protective tube
- PROFINET type B for flexible use
- Robust cable for use in harsh environments

Commercial data

Item number	1500186
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOBS
GTIN	4063151955090
Weight per piece (including packing)	1,728.841 g
Weight per piece (excluding packing)	1,728.841 g
Customs tariff number	85447000
Country of origin	DE

1500186

<https://www.phoenixcontact.com/us/products/1500186>

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Number of positions	2
Cable outlet	straight

Interfaces

Signal type/category	Ethernet
----------------------	----------

Electrical properties

Transmission medium	PCF fiber
---------------------	-----------

Connector

Connection 2

Type	Plug
------	------

Cable/line

Cable length	18.00 m
Cable weight	45 kg/km
External cable diameter	7.2 mm
Outer sheath, material	PVC
External sheath, strain relief elements	Non-metallic, aramide fiber
Single wire, number of litz wires	2
Single wire, material	PVC
Individual wire diameter	2.2 mm ±0.1 mm
Tensile strength short-term/long-term	800 N / 100 N
Lateral pressure short term	500 N/cm
Lateral pressure, long-term	300 N/cm
Bending radius, single element	30 mm (Short-term)
	30 mm (Short-term)
Bending radius, entire cable	70 mm (Short-term)
	70 mm (Short-term)
660 nm	10 dB/km
850 nm	8 dB/km
Resistance to oil	very good oil and chemical resistance
Behavior in fire	Flame-resistant as per IEEE and IEC 60 332-3 test type C

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

1500186

<https://www.phoenixcontact.com/us/products/1500186>

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 10.0	EC002700
-----------	----------

1500186

<https://www.phoenixcontact.com/us/products/1500186>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com