

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting



1456132

<https://www.phoenixcontact.com/us/products/1456132>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device connector rear mounting, 6-position, Socket, straight, M8, A-coding, Wave soldering



Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- Standard pin assignments and codings for signal transmission with a uniform design-in design
- For high transmission reliability: optional shield connection to the housing and latching on the PCB

Commercial data

Item number	1456132
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQJAB
GTIN	4046356605755
Weight per piece (including packing)	6.73 g
Weight per piece (excluding packing)	6.5 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting



1456132

<https://www.phoenixcontact.com/us/products/1456132>

Technical data

Mounting

Mounting type	Rear mounting (M10, with flat nut)
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

Product properties

Product type	Circular connectors (device side)
Application	Data
Number of positions	6
Shielded	yes
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	Cu alloy
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

Electrical properties

Rated surge voltage	0.8 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	1.5 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

Mechanical properties

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting



1456132

<https://www.phoenixcontact.com/us/products/1456132>

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
	-25 °C ... 85 °C (without mechanical actuation)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting




1456132

<https://www.phoenixcontact.com/us/products/1456132>

Drawings

Schematic diagram



Pin assignment M8 socket, 6-pos.

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting




1456132

<https://www.phoenixcontact.com/us/products/1456132>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1456132>

 cUL Recognized Approval ID: E221474-20070307				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	26	-

 UL Recognized Approval ID: E221474-20070307				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	1.5 A	26	-

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting



1456132

<https://www.phoenixcontact.com/us/products/1456132>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M8FS-6CON-M10-L180 SH - Device connector rear mounting



1456132

<https://www.phoenixcontact.com/us/products/1456132>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f92385c1-38a4-4470-be19-58965581b8bc

EF3.1 Climate Change

CO2e kg	1.247 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com