# SACC-DSI-MS-8CON-L180/SH TQ - Device connector rear mounting

1456530

https://www.phoenixcontact.com/us/products/1456530

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 8-position, Pin, straight, M12-SPEEDCON, A-coding, Wave soldering, this item is expected to be lead-free from Q3 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

| | |
|---|---|
| Item number | 1456530 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | AB26 |
| Product key | ABQEGB |
| GTIN | 4046356617154 |
| Weight per piece (including packing) | 14.435 g |
| Weight per piece (excluding packing) | 13.056 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

## Technical data

### Notes

| | |
|---|---|
| Order information: | Lock nut is included in the scope of delivery |

### Mounting

| | |
|---|---|
| Mounting type | Rear mounting (M16 x 1.5, with flat nut) |

### Product properties

| | |
|---|---|
| Product type | Circular connectors (device side) |
| Application | Data |
| Number of positions | 8 |
| Shielded | yes |
| Coding | A |
| Thread type | M12 |

#### Insulation characteristics

| | |
|---|---|
| Overvoltage category | II |
| Degree of pollution | 3 |

### Dimensions

| | |
|---|---|
| Length of the solder pin | 6 mm |
| | 6 mm |

### Material specifications

| | |
|---|---|
| Material Housing | GD-Zn |
| Material Housing surface | Ni |
| Material Contact carrier | PA 6.6 |
| Material Contact | CuZn |
| Material Contact surface | Au |
| Material Seal | FKM |
| Flammability rating according to UL 94 | V0 |

### Electrical properties

| | |
|---|---|
| Rated surge voltage | 0.8 kV |
| Contact resistance | ≤ 3 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage $U_N$ | 48 V AC |
| | 60 V DC |
| Nominal current $I_N$ | 2 A |
| Transmission characteristics (category) | CAT5 (IEC 11801:2002) |

### Connection data

Conductor connection

| | |
|---|---|
| Connection method | Wave soldering |
| Contact connection type | Pin |

## Mechanical properties

Mechanical data

| | |
|---|---|
| Insertion/withdrawal cycles | ≥ 100 |

## Connector

Connection 1

| | |
|---|---|
| Head design | Pin |
| Head cable outlet | straight |
| Head thread type | M12 |
| Head locking type | SPEEDCON |
| Coding | A |

## Environmental and real-life conditions

Ambient conditions


| | |
|---|---|
| Degree of protection | IP67 (When plugged in) |
| | IP65 (When plugged in) |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C |
| UL Type Rating | Type 4 (indoor use only) |

## Standards and regulations

| | |
|---|---|
| Standard designation | M12 circular connector |
| Standards/specifications | according to IEC 61076-2-101 |

## Drawings

Schematic diagram




Pin assignment M12 plug, 8-pos., view plug side

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1456530

**UL Recognized**
Approval ID: E118976-20100522

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 30 V | 2 A | 24 | - |

**cULus Recognized**
Approval ID: E221474-20140616

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 30 V | 2 A | - | - |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440110 |
| ECLASS-15.0 | 27440110 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC003568 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 8b03246a-caaa-4d27-a51f-131ad73c056d |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com