

# SAC-4P-100,0-PVC/0,34 - Cable reel



1501838

<https://www.phoenixcontact.com/us/products/1501838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Cable reel, PVC, black RAL 9005, 4-wire, color single wire: brown, white, blue, black, cable length: 100 m



## Commercial data

Item number	1501838
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF11
Product key	AF1LBA
GTIN	4017918813963
Weight per piece (including packing)	3,420 g
Weight per piece (excluding packing)	3,003.12 g
Customs tariff number	85444995
Country of origin	DE

# SAC-4P-100,0-PVC/0,34 - Cable reel

1501838

<https://www.phoenixcontact.com/us/products/1501838>

## Technical data


### Product properties

Product type	Cable by the meter
Application	Connector
Number of positions	4
Shielded	no

### Cable/line

Cable length	100 m
--------------	-------

### PVC black [PVC]

Dimensional drawing	
Cable weight	40 kg/km
UL AWM Style	2464 / 1729 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross-section	4x 0.34 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.26 mm ±0.05 mm
External cable diameter	4.70 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	4 wires, twisted
Max. conductor resistance	≤ 57 Ω/km (at 20 °C)
Insulation resistance	≥ 200 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D

# SAC-4P-100,0-PVC/0,34 - Cable reel



1501838

<https://www.phoenixcontact.com/us/products/1501838>

Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	24 mm
Smallest bending radius, movable installation	47 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	according to DIN EN 60811-2-1, 168 h at 60 °C
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-10 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-100,0-PVC/0,34 - Cable reel



1501838

<https://www.phoenixcontact.com/us/products/1501838>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1501838>



**EAC-RoHS**

Approval ID: RU D-DE.HB35.B.00371

# SAC-4P-100,0-PVC/0,34 - Cable reel



1501838

<https://www.phoenixcontact.com/us/products/1501838>

## Classifications

### ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

### ETIM

ETIM 10.0	EC003249
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-4P-100,0-PVC/0,34 - Cable reel



1501838

<https://www.phoenixcontact.com/us/products/1501838>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	28.003 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)