

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Double valve connector cable, 4-position, PUR/PVC, black, free cable end, on Valve connector BI (11 mm), with 1 LED, Wiring: Z diode and Valve connector BI (11 mm), with 1 LED, Wiring: Z diode, cable length: 5 m, valve connector spacing: 0.1 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Efficient: control valves with two connections via a single connecting cable
- Convenient: increased machine availability thanks to quick and easy diagnostics

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1458363 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF07 |
| Product key | AF1DIA |
| GTIN | 4046356638807 |
| Weight per piece (including packing) | 366.6 g |
| Weight per piece (excluding packing) | 364.1 g |
| Customs tariff number | 85444290 |
| Country of origin | PL |

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

Technical data

Product properties

| | |
|----------------------|--|
| Product type | Sensor/actuator cable with valve connector |
| Application | Standard |
| Number of positions | 4 |
| No. of cable outlets | 1 |
| Shielded | no |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Connection data

Conductor connection

| | |
|-------------------|--------|
| Tightening torque | 0.6 Nm |
|-------------------|--------|

Material specifications

| | |
|--|--------|
| Flammability rating according to UL 94 | HB |
| Seal material | TPU |
| Material housing valve plug | TPU |
| Contact material | CuSn |
| Valve plug contact insert material | PA 6.6 |
| Contact surface material | Sn |

Electrical properties

| | |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 24 V AC |
| | 24 V DC |
| Nominal current I_N | 4 A |

Valve connector characteristics

| | |
|------------------|---|
| Fixing screws | M3 x 29 |
| Pulse power | 40 W (at 100 μs square-wave pulse) |
| Terminal voltage | 70 V (at 2 mA constant current) |
| Reverse voltage | 50 V |

Mechanical properties

Mechanical data

| | |
|-----------------------------|----|
| Insertion/withdrawal cycles | 50 |
|-----------------------------|----|

Signaling

| | |
|------------------------|-------|
| Status display | 1 LED |
| Status display present | yes |

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

Connector

Connection 1

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

Connection 2

| | |
|--------------------|----------------------------|
| Type | Valve connector BI (11 mm) |
| Material | CuSn (Contact) |
| | Sn (Contact surface) |
| | PA 6.6 (Contact carrier) |
| | TPU (Housing) |
| Protective circuit | Z diode |

Connection 3

| | |
|--------------------|----------------------------|
| Type | Valve connector BI (11 mm) |
| Material | CuSn (Contact) |
| | Sn (Contact surface) |
| | PA 6.6 (Contact carrier) |
| | TPU (Housing) |
| Protective circuit | Z diode |

Cable/line

| | |
|--------------|-------|
| Cable length | 5 m |
| | 0.1 m |

PUR/PVC, 0.75 mm², black [116]

| | |
|---------------------------------|--|
| Dimensional drawing |  |
| Cable weight | 57 kg/km |
| UL AWM Style | 20549 |
| Number of positions | 4 |
| Shielded | no |
| Cable type | PUR/PVC, 0.75 mm ² , black [116] |
| Conductor structure signal line | 24x 0.20 mm |
| AWG signal line | 18 |
| Conductor cross-section | 4x 0.75 mm ² |
| Wire diameter incl. insulation | 1.7 mm ±0.05 mm |
| External cable diameter | 6.30 mm ±0.2 mm |
| Outer sheath, material | PUR |

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

| | |
|---|--|
| External sheath, color | black |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PVC |
| Single wire, color | black 1, black 2, black 3, green/yellow |
| Overall twist | 4 wires, twisted |
| Max. conductor resistance | 26 Ω /km (at 20 °C) |
| Insulation resistance | ≥ 20 M Ω *km |
| Nominal voltage, cable | 300 V |
| Test voltage | 1200 V |
| Smallest bending radius, fixed installation | 63 mm |
| Flame resistance | according to DIN VDE 0482 |
| | According to DIN EN 50265-2-1 |
| | in acc. with UL FT-2 |
| Ambient temperature (operation) | -5 °C ... 80 °C (Cable, flexible installation) |
| | -40 °C ... 80 °C (cable, fixed installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) (Valve connector) | -25 °C ... 85 °C (Valve connector) |

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable

1458363

<https://www.phoenixcontact.com/us/products/1458363>

Drawings

Dimensional drawing



Double valve plug, 2 x type BI

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable

1458363

<https://www.phoenixcontact.com/us/products/1458363>

Dimensional drawing



Valve connector spacing

Schematic diagram



Valve connector pin assignment, type BI

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable

1458363

<https://www.phoenixcontact.com/us/products/1458363>

Circuit diagram



Contact assignment of the double-valve connector

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1458363>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387



CSAus

Approval ID: 13631

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 24 V | 6 A | - | - |

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060312 |
| ECLASS-15.0 | 27060312 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31251500 |
|-------------|----------|

SAC- 5,0/0,1-116/2XBI-1L-Z - Double valve connector cable



1458363

<https://www.phoenixcontact.com/us/products/1458363>

Environmental product compliance

EU RoHS

| | |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 3.74 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com