

CUC-V14-C1ZNI-T/R4IV8 - RJ45 connector



1464018

<https://www.phoenixcontact.com/us/products/1464018>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 2, CAT5 (IEC 11801:2002), material: Metal, connection method: IDC fast connection, cable outlet: angled, VARAN

Your advantages

- Push-pull ADVANCE connector
- Locking system to prevent inadvertent release
- Protected data transmission thanks to 360° shielding concept
- Highest ESD and EMC resistance for reliable transmission

Commercial data

Item number	1464018
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABNOAA
GTIN	4046356790048
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

CUC-V14-C1ZNI-T/R4IV8 - RJ45 connector



1464018

<https://www.phoenixcontact.com/us/products/1464018>

Technical data

Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	VARAN
Number of positions	2
Shielded	no
Cable outlet	angled

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

Connection data

Connection technology

Connection method	IDC fast connection
-------------------	---------------------

Dimensions

Width	22.4 mm
Height	49.2 mm
Length	100 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	nickel-plated

Cable/line

External cable diameter	5.5 mm ... 10 mm
Cable cross section	0.14 mm ²

Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

CUC-V14-C1ZNI-T/R4IV8 - RJ45 connector



1464018

<https://www.phoenixcontact.com/us/products/1464018>

Classifications

ECLASS

ECLASS-13.0	27440116
-------------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1464018

<https://www.phoenixcontact.com/us/products/1464018>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	13819481-3318-4b88-aa0f-214a09443f94

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com