

PTCB E1 24DC/0.63A SI-R - Electronic circuit breaker




1464485

<https://www.phoenixcontact.com/us/products/1464485>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Single-channel, electronic device protection for 12-24 V DC loads. Fixed nominal current value: 0.63 A. With remote signaling, remote reset, and active current limitation. Can be combined with CLIPLINE terminal blocks. For installation on DIN rails.



Your advantages

- Precise fault localization and fast recovery thanks to status message and local and remote reset options
- Effortless system planning due to precise shutdown and low voltage losses
- More space in the control cabinet due to integrated potential distribution of positive and negative in 6 mm
- Simple application setup due to bridging option to CLIPLINE complete terminal block system

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1464485 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL10 |
| Product key | CLA135 |
| GTIN | 4063151857547 |
| Weight per piece (including packing) | 32 g |
| Weight per piece (excluding packing) | 25.84 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

1464485

<https://www.phoenixcontact.com/us/products/1464485>

Technical data

Notes

General

| | |
|------|--|
| Note | Connection for signal line tested in accordance with EN 61000-4-4 with 1 kV; if necessary, customer must provide appropriate protective measures |
| | Repeated hard short circuits can reduce the melting integral of the integrated backup fuse. |

Product properties

| | |
|---------------------|----------------------------|
| Product type | Device circuit breakers |
| Product family | PTCB |
| Type | DIN rail module, one-piece |
| Number of positions | 1 |
| No. of channels | 1 |

Insulation characteristics

| | |
|------------------|-----|
| Protection class | III |
| Pollution degree | 2 |

Electrical properties

General

| | |
|----------------------------------|---|
| Operating voltage | 10 V DC ... 30 V DC |
| Rated voltage | 12 V DC 24 V DC |
| Rated current I_N | 15 A (Total current input) 0.63 A (Rated current output) |
| Rated current I_N | 0.63 A DC |
| Rated current (pre-adjusted) | 0.63 A |
| Rated surge voltage | 0.5 kV |
| Tripping method | E (electronic) |
| Feedback resistance | max. 35 V DC |
| Required backup fuse | Only required if I_{max} of the power supply > the short-circuit switching capacity. Integrated failsafe element. |
| Short-circuit switching capacity | 300 A |
| Dielectric strength | max. 35 V DC (Load circuit) |
| Active current limitation | typ. $1,08 \times I_N$ |
| Fuse | electronic |
| Efficiency | > 98.5 % |
| Closed circuit current I_0 | typ. 3.8 mA |
| Power dissipation | typ. 0.1 W (No-load operation) < 0.7 W (Nominal operation) |
| Module initialization time | 40 ms |

PTCB E1 24DC/0.63A SI-R - Electronic circuit breaker



1464485

<https://www.phoenixcontact.com/us/products/1464485>

| | |
|--|---|
| Waiting time after switch off of a channel | 5 s (at overload / short circuit) |
| Measuring tolerance I | ± 7 % |
| Temperature derating | 15 A (Total current at 60°C) 20 A (Total current at 50°C) |
| MTBF (IEC 61709, SN 29500) | 27034333 h (at 25 °C with 21 % load) 11609008 h (at 40°C with 34.25% load) 1631800 h (at 60°C with 100% load) |
| Voltage drop | 0.35 V (at 0.63 A) |
| Fail-safe element | 4 A DC |
| Contact switching type | without electrical isolation |

Load circuit

| | |
|-------------------------|---|
| Shutdown time | ≤ 600 ms |
| | ≥ 12 ms (depending on the available load) |
| | Shutdown, typical, $1.08 \times I_N$ |
| Undervoltage switch-off | ≤ 9.2 V DC (active) |
| | ≥ 10.2 V DC (inactive) |
| Overvoltage switch-off | ≥ 30.5 V DC (active) |
| | ≤ 29.5 V DC (inactive) |
| Max. capacitive load | 4.7 mF (Depending on the current setting and the short-circuit current available) |

Reset

| | |
|---|--|
| Input voltage range | 7 V DC ... 30 V DC (Reset with falling edge) |
| Current consumption | typ. 0.4 mA (at 24 V DC) |
| Pulse length | ≥ 50 ms (High) |
| | ≥ 50 ms (Low) |
| Voltage | < 5 V DC (Low state) |
| | > 8 V DC (High state) |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm ² ... 2.5 mm ² |

Status output

| | |
|---|--|
| Output voltage | 24 V DC (Error) |
| | 0 V DC (no error) |
| Output current | max. 0.015 A (Short-circuit-proof) |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm ² ... 2.5 mm ² |

1464485

<https://www.phoenixcontact.com/us/products/1464485>

Connection data

Main circuit IN+

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.2 mm ² ... 2.5 mm ² |

Main circuit IN-

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.2 mm ² ... 2.5 mm ² |

Main circuit OUT

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.2 mm ² ... 2.5 mm ² |

Signaling

| | |
|--------------------|--|
| Channel LED off | off (Channel switched off) |
| Channel LED yellow | flashing (Programming mode active) |
| Channel LED green | lit (Channel switched on) |
| Channel LED red | lit (Channel switched off, over- or undervoltage active) |
| | ON temporarily (Channel switched off, 5 s cool-down phase, overload or short-circuit release) |
| | flashing (Channel switched off, ready to be switched back on, overload or short-circuit release) |
| | flashing quickly (Channel switched off, external voltage at the output, possible installation error) |

Dimensions

PTCB E1 24DC/0.63A SI-R - Electronic circuit breaker



1464485

<https://www.phoenixcontact.com/us/products/1464485>

| | |
|---------------------|---------------------------------|
| Dimensional drawing | |
| Width | 6.2 mm |
| Height | 105.8 mm |
| Depth | 55.6 mm (incl. DIN rail 7.5 mm) |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Material | PBT |
| | PBT |
| Flammability rating according to UL 94 | V-0 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -30 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Altitude | ≤ 3000 m up to 52 °C (amsl) ≤ 4000 m up to 46 °C (amsl) |
| Humidity test | 96 h, 95 % RH, 40 °C |
| Shock (operation) | 30g (IEC 60068-2-27, Test Ea) |
| Vibration (operation) | 10 Hz ... 59.6 Hz (Amplitude ±0.35 mm; in accordance with IEC 60068-2-6, Test Fc) 59.6 Hz ... 150 Hz (Acceleration 5g; in accordance with IEC 60068-2-6, Test Fc) 5 Hz ... 100 Hz (Resonance search 4g; resonance frequency 4g; 90 min in accordance with DNV GL Class B) |

Approvals

UL approval

| | |
|----------------|---|
| Identification | UL/C-UL Listed UL 508 UL Recognized UL 2367 NEC Class 2 according to UL 1310 UL/C-UL Listed ANSI/UL 121201 Class I, Division 2, Groups A, B, C, D (Hazardous Location) |
|----------------|---|

DNV GL

| | |
|----------------|-----------------------|
| Identification | Shipbuilding approval |
|----------------|-----------------------|

Corrosive gas test

| | |
|----------------|----------------------------------|
| Identification | ISA S71.04.2013 G3 Harsh Group A |
|----------------|----------------------------------|

Shipbuilding data

1464485

<https://www.phoenixcontact.com/us/products/1464485>

| | |
|-------------|---|
| Temperature | A |
| Humidity | B |
| Vibration | B |
| EMC | A |
| Enclosure | A |

Standards and regulations

| | |
|--------------------------|---|
| Standards/specifications | EN 61000-6-2 |
| Note | EMC – Immunity for industrial areas |
| Standards/specifications | EN 61000-6-3 |
| Note | EMC – Emission for residential, business and commercial properties and small operations |
| Standards/specifications | EN 60068-2-78 |
| Note | Environmental influences – Moisture and heat, constant |
| Standards/specifications | EN 50178 |
| Note | Equipping power installations with electronic equipment |
| Standards/specifications | EN 60068-2-6 |
| Note | Environmental influences – Vibrations (sinusoidal) |
| Standards/specifications | EN 60068-2-27 |
| Note | Environmental influences – Shocks |
| Standards/specifications | EN 60068-2-30 |
| Note | Environmental influences – Part 2–30: Tests – Test Db: Damp heat, cyclical |

Mounting

| | |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|

PTCB E1 24DC/0.63A SI-R - Electronic circuit breaker



1464485

<https://www.phoenixcontact.com/us/products/1464485>

Drawings

Dimensional drawing



Diagram



Total current input

PTCB E1 24DC/0.63A SI-R - Electronic circuit breaker



1464485

<https://www.phoenixcontact.com/us/products/1464485>

Block diagram



1464485

<https://www.phoenixcontact.com/us/products/1464485>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1464485>



UL Recognized

Approval ID: E317172-20170817



UL Listed

Approval ID: E123528-20170530



cUL Listed

Approval ID: E123528-20170530



DNV GL

Approval ID: TAE00003UT



UL Recognized

Approval ID: E324415-20201030



cUL Listed

Approval ID: E483407-20201030



UL Listed

Approval ID: E483407-20201030

PTCB E1 24DC/0.63A SI-R - Electronic circuit breaker



1464485

<https://www.phoenixcontact.com/us/products/1464485>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140401 |
| ECLASS-15.0 | 27140401 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003538 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1464485

<https://www.phoenixcontact.com/us/products/1464485>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 5385a556-3a9f-4d88-92c1-a068b240b5a9 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.195 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com