

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in surge protective device, in accordance with type 2/class II, for 1-phase power supply networks with combined installation of PE and N in one conductor (2-conductor system: L, N/PEN).

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466558
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL18
Product key	CL1381
GTIN	4063151860721
Weight per piece (including packing)	146.65 g
Weight per piece (excluding packing)	124.4 g
Customs tariff number	85363030
Country of origin	DE

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

Technical data

Notes

General

Note	For pollution degree 3 and wiring with fork cable lugs, an additional minimum lateral distance of 1 mm to earthed conductive surfaces must be maintained for cross-sections $\geq 16 \text{ mm}^2$. No additional lateral distances are required for pollution degree 2.
------	--

Product properties

Product type	Surge arrester
Product family	VAL-SPP
IEC test classification	II
	T2
EN type	T2
IEC power supply system	TN
	TT
Type	DIN rail module, two-section, divisible
Number of positions	1
End-of-life mode	OCM
Surge protection fault message	optical, remote signaling via optional module
Number of ports	One

Insulation characteristics

Overvoltage category	III
Pollution degree	3

Electrical properties

Maximum power dissipation for nominal condition	$\leq 150 \text{ mVA}$
Nominal frequency f_N	50 Hz (60 Hz)

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm ... 3.5 Nm
Stripping length	18 mm
Conductor cross-section flexible	1.5 mm ² ... 35 mm ² (without ferrule)
	2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Conductor cross-section rigid	1.5 mm ² ... 50 mm ²
	2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Conductor cross-section AWG	15 ... 2

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 16 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	1.5 mm ² ... 35 mm ² 2x 1.5 mm ² ... 10 mm ² (2 conductors with the same cross-section)
Conductor cross-section, flexible, with ferrule, without plastic sleeve	1.5 mm ² ... 25 mm ² 2x 1.5 mm ² ... 16 mm ² (2 conductors with the same cross-section)
Connection method	Fork-type cable lug
Conductor cross-section flexible	1.5 mm ² ... 25 mm ²

Dimensions

Dimensional drawing	
Width	17.8 mm
Height	96.6 mm
Depth	71.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

Material specifications

Color	gray (RAL 7042) light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF PBT
Material group	I
Housing material	PA 6.6-FR 20 % GF PBT

Protective circuit

Mode of protection	L-N L-PEN
Nominal voltage U_N	240 V AC ± 10 % (TN) 240 V AC ± 10 % (TT)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous operating voltage U_C	335 V AC
Rated load current I_L	80 A (25 mm ²)
Nominal discharge current I_n (8/20) μ s	20 kA
Maximum discharge current I_{max} (8/20) μ s	40 kA
Short-circuit current rating I_{SCCR}	50 kA
Voltage protection level U_p	≤ 1.5 kV

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

Residual voltage U_{res}	≤ 1.5 kV (at I_n)
	≤ 1.3 kV (at 10 kA)
	≤ 1.2 kV (at 5 kA)
	≤ 1.1 kV (at 3 kA)
TOV behavior at U_T	415 V AC (5 s / withstand mode)
	460 V AC (120 min / safe failure mode)
Response time t_A	≤ 25 ns
Max. backup fuse with V-type through wiring	80 A (gG)
Max. backup fuse with branch wiring	315 A (gG)

Additional technical data

Short-circuit current rating I_{SCCR}	100 kA
---	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

Approvals

UL specifications

Maximum continuous operating voltage MCOV	335 V AC
Nominal discharge current I_n	20 kA
Mode of protection	Ld-Ld
Nominal voltage	240 V AC
Power distribution system	Single phase
Nominal frequency	50/60 Hz
Measured limiting voltage MLV	1340 V
SPD Type	4CA

UL connection data

Tightening torque	30 lb _F in.
Conductor cross-section AWG	14 ... 2

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012 + A11:2018

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester


1466558

<https://www.phoenixcontact.com/us/products/1466558>



Drawings

Dimensional drawing



Schematic diagram



Pollution degree	Conductor cross section	2		3	
		Altitude		Altitude	
		≤4000 m	5000 m	≤4000 m	5000 m
	≥50 mm ²	-	-	-	-
	≥35 mm ²	-	-	-	-
	≥25 mm ²	-	-	-	-
	≥16 mm ²	-	1 mm	1 mm	1 mm

Table 1: Minimum lateral distance to active and grounded conductive parts


1466558

<https://www.phoenixcontact.com/us/products/1466558>



Max. permissible current in relation to the ambient temperature

Circuit diagram



VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1466558>

DNV

Approval ID: TAE0000501



IECEE CB Scheme

Approval ID: NL-118261



cULus Recognized

Approval ID: E330181

DEKRA

Approval ID: 71-161244

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558

<https://www.phoenixcontact.com/us/products/1466558>

Classifications

ECLASS

ECLASS-13.0	27171202
ECLASS-15.0	27171202

ETIM

ETIM 10.0	EC000941
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

VAL-SPP-T2-335-1+0-UT - Type 2 surge arrester



1466558
<https://www.phoenixcontact.com/us/products/1466558>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com