

OCS FOOT SET - Wall bracket

1471777

<https://www.phoenixcontact.com/us/products/1471777>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting foot, set of 4 pieces incl. screws for all housing sizes, material: polycarbonate, color: light gray



Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1471777 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC04 |
| Product key | ACFDBZ |
| GTIN | 4063151880859 |
| Weight per piece (including packing) | 85 g |
| Weight per piece (excluding packing) | 85 g |
| Customs tariff number | 39269097 |
| Country of origin | EE |

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Technical data

Notes

| | |
|---------------|--|
| Assembly note | Only use the screws supplied for mounting. |
| Assembly note | You can mount the mounting feet in 3 different positions. |
| Assembly note | Secure the mounting feet or flanges using the screws provided. If mounting the housing on a wall, select the appropriate screw type for the wall construction. |

Product properties

| | |
|----------------|-------------------|
| Product type | Mounting material |
| Housing type | Outdoor housing |
| Housing type | Outdoor housings |
| Housing series | OCS |

Dimensions

| | |
|--------|-------|
| Width | 45 mm |
| Height | 65 mm |
| Depth | 10 mm |

Material specifications

| | |
|--|-----------------------|
| Color | light gray (RAL 7035) |
| Material | PC |
| Flammability rating according to UL 94 | V2 |
| Insulating material | PC |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 80 °C |
|---------------------------------|------------------|

Mounting

| | |
|---------------|---------------------------------|
| Mounting type | Mast mounting or panel mounting |
|---------------|---------------------------------|

Packaging specifications

| | |
|-------------------|--------|
| Type of packaging | PE bag |
|-------------------|--------|

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1471777>

FI Cert

Approval ID: FI/42054

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

OCS FOOT SET - Wall bracket



1471777

<https://www.phoenixcontact.com/us/products/1471777>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com