

RCK-TWGM/BL16+3/ 5,0PUR SH - Master cable



1519529

<https://www.phoenixcontact.com/us/products/1519529>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Master cable, application: Sensor/actuator box, number of positions: 19, slot assignment: Double, status display: no; master cable connection: M23 plug connection, PUR/PVC, cable length: 5 m, shielding: yes, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1519529
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB34
Product key	ABRDCB
GTIN	4017918940140
Weight per piece (including packing)	1,274.8 g
Weight per piece (excluding packing)	1,089.04 g
Customs tariff number	85444290
Country of origin	DE

1519529

<https://www.phoenixcontact.com/us/products/1519529>

Technical data

Notes

Notes on operation	The master cable is earmarked for use on the sensor/actuator boxes with an M23 plug-in connection.
--------------------	--

Product properties

Product type	Master cable, assembled
Application	Sensor/actuator box
Number of positions	19

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Connection data

Connection method	Fixed connection
-------------------	------------------

Signaling

Status display present	no
------------------------	----

Material specifications

Material Housing	PUR
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	PA
Material of contact surface, master cable side	gold-plated

Connector

Connection 1

Head design	Socket
Head cable outlet	angled
Head thread type	M23

Connection 2

Head design	free cable end
-------------	----------------

Cable/line

Cable length	5 m
--------------	-----


PUR/PVC shielded, black [PUR]

RCK-TWGM/BL16+3/ 5,0PUR SH - Master cable



1519529

<https://www.phoenixcontact.com/us/products/1519529>

Dimensional drawing	
Number of positions	19
Shielded	yes
Cable type	PUR/PVC shielded, black [PUR]
Conductor structure signal line	64x 0.10 mm
AWG signal line	20
Conductor structure, voltage supply	128x 0.10 mm
AWG power supply	17
Conductor cross-section	16x 0.5 mm ² (Signal line) 3x 1 mm ² (Power supply)
Wire diameter incl. insulation	1.6 mm (Signal line) 2 mm (power line)
External cable diameter	11.60 mm ±0.3 mm
Outer sheath, material	PUR
External sheath, color	deep black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet, gray/pink, red/blue, white/green, brown/green, white/yellow, yellow/brown, white/gray, gray/brown
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V
Test voltage	2000 V
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 10 x D, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

RCK-TWGM/BL16+3/ 5,0PUR SH - Master cable



1519529

<https://www.phoenixcontact.com/us/products/1519529>

	IP67
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 125 °C (Plug / socket)

Drawings

Schematic diagram



Pin assignment M23 socket, 19-pos., female side view

Circuit diagram



Circuit diagram

RCK-TWGM/BL16+3/ 5,0PUR SH - Master cable



1519529

<https://www.phoenixcontact.com/us/products/1519529>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1519529>



EAC

Approval ID: 19060508

RCK-TWGM/BL16+3/ 5,0PUR SH - Master cable



1519529

<https://www.phoenixcontact.com/us/products/1519529>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

1519529

<https://www.phoenixcontact.com/us/products/1519529>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9f7288a8-3312-4945-8908-71c969b6be57

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com