

CBC-PRC COVER M 800V - Protective cap



1476945

<https://www.phoenixcontact.com/us/products/1476945>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cap, Range of articles: ArcZero, color: black, rated voltage: 800 VDC, Fit the protective cap when not plugged in., scope: DC grid

Your advantages

- Safe connection and disconnection under load
- Fast disconnection of flying leads
- Time-saving maintenance or replacement of connected devices
- Robust outdoor design even for extreme conditions
- Particularly durable and economical

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1476945 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB03 |
| Product key | ABLFZA |
| GTIN | 4063151889890 |
| Weight per piece (including packing) | 7.6 g |
| Weight per piece (excluding packing) | 5.369 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

CBC-PRC COVER M 800V - Protective cap



1476945

<https://www.phoenixcontact.com/us/products/1476945>

Technical data

Notes

| | |
|-----------------|---|
| Notes on safety | Fit the protective cap when not plugged in. |
|-----------------|---|

Product properties

| | |
|---------------------|----------------|
| Product type | Protective cap |
| Product family | ArcZero |
| Area of application | DC grid |

Insulation characteristics

| | |
|------------------|----------------------|
| Protection class | II (plastic housing) |
|------------------|----------------------|

Electrical properties

| | |
|---------------|---|
| Rated voltage | 800 VDC (III/2.00) in accordance with IEC 61984 |
| | 250 VDC Minimum system voltage |
| | 500 VDC (III/2.00) in accordance with IEC 61535 |
| | 600 VDC (III/2.00) in accordance with UL 2238 / UL 2237 |

Dimensions

| | |
|--------|---------|
| Width | 37.8 mm |
| Height | 26.4 mm |
| Length | 35.5 mm |

Material specifications

| | |
|-------------------------|-------|
| Color | black |
| Material Protective cap | PPE |

Cable/line

| | |
|--------------|---|
| Halogen-free | yes (in accordance with IEC 61249-2-21:2003- 11 Cl.3.1) |
|--------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Degree of protection | IP66 |
| | IP68 (2 m / 2 h) |
| | IP69 |
| Ambient temperature (operation) | -40 °C ... 105 °C |
| Ambient temperature (storage/transport) | -40 °C ... 105 °C |
| Ambient temperature (assembly) | -40 °C ... 105 °C |

Standards and regulations

| | |
|--------------------------|----------------|
| Standards/specifications | IEC 61984 |
| | IEC TS 62735-1 |

CBC-PRC COVER M 800V - Protective cap



1476945

<https://www.phoenixcontact.com/us/products/1476945>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440691 |
| ECLASS-15.0 | 27440691 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002863 |
|-----------|----------|

CBC-PRC COVER M 800V - Protective cap



1476945

<https://www.phoenixcontact.com/us/products/1476945>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Triphenyl phosphate(CAS: 115-86-6) |
| SCIP | f11ca4a4-467d-47f6-85d0-50f19201a3de |

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.06 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com