

SACC-DSIV-M 8FS-4CON-L180-06 - Device connector rear mounting



1524789

<https://www.phoenixcontact.com/us/products/1524789>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Socket, straight, M8, A-coding, Wave soldering

Your advantages

- Standard pin assignments and codings for signal transmission with a uniform design-in design

Commercial data

Item number	1524789
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB22
Product key	ABQJBG
GTIN	4017918950095
Weight per piece (including packing)	5.1 g
Weight per piece (excluding packing)	3.47 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIV-M 8FS-4CON-L180-06 - Device connector rear mounting



1524789

<https://www.phoenixcontact.com/us/products/1524789>

Technical data

Mounting

Mounting type	Rear mounting (M8 x 1, with locking nut)
---------------	--

Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	no
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Insulating body	PA 6.6
Material Contact	CuSn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
Head cable outlet	straight

SACC-DSIV-M 8FS-4CON-L180-06 - Device connector rear mounting



1524789

<https://www.phoenixcontact.com/us/products/1524789>

Head thread type	M8
Coding	A

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
Ambient temperature (operation)	-25 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

SACC-DSIV-M 8FS-4CON-L180-06 - Device connector rear mounting




1524789

<https://www.phoenixcontact.com/us/products/1524789>

Drawings

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

SACC-DSIV-M 8FS-4CON-L180-06 - Device connector rear mounting



1524789

<https://www.phoenixcontact.com/us/products/1524789>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIV-M 8FS-4CON-L180-06 - Device connector rear mounting



1524789

<https://www.phoenixcontact.com/us/products/1524789>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	35484a0a-cf23-4768-894d-05475ff64188

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com