

# SACC-M 8MS-4PL-M - Connector



1482520

<https://www.phoenixcontact.com/us/products/1482520>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 4-position, unshielded, Plug straight M8, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 3.5 mm ... 5.5 mm

## Your advantages

- Time-saving Push-Lock connection: Tool-free connection and disconnection of conductors by opening the contact levers
- Intuitive connection: Easy assignment of individual litz wires with color-coded and numerical identification of the contact levers
- Integrated Push-in Technology: Wire rigid and pretreated conductors easily by means of simple, direct insertion
- Shock- and vibration-resistant connection: Proven spring-cage technology guarantees secure and reliable contacting
- Safe use in the field, thanks to a high degree of protection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1482520       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF33          |
| Product key                          | AF2BEA        |
| GTIN                                 | 4067923233652 |
| Weight per piece (including packing) | 13 g          |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-M 8MS-4PL-M - Connector

1482520

<https://www.phoenixcontact.com/us/products/1482520>



## Technical data

### Notes

|               |                                                                                                                                                                                                                                                                                              |
|---------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.                                                      |
| General       | The user must take appropriate safety precautions so that the connector cannot be accidentally loosened or opened. To protect against unintentional opening of the connector, the thread must be secured between the housing and the connector head using a suitable cyanoacrylate adhesive. |


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Number of positions  | 4                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 14 mm                                                                                |
| Height              | 14 mm                                                                                |
| Length              | 51 mm                                                                                |

### External dimensions

|                  |                   |
|------------------|-------------------|
| Outside diameter | 3.5 mm ... 5.5 mm |
|------------------|-------------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 14 mm |
|------------------|-------|

### Material specifications

|                                        |                        |
|----------------------------------------|------------------------|
| Material                               | PBT                    |
|                                        | PA 6 (Actuation lever) |
| Flammability rating according to UL 94 | V0                     |
| Seal material                          | NBR                    |

# SACC-M 8MS-4PL-M - Connector



1482520

<https://www.phoenixcontact.com/us/products/1482520>

|                               |                              |
|-------------------------------|------------------------------|
| Material of grip body         | PA 6.6                       |
| Contact material              | CuSn                         |
| Contact surface material      | Ni/Au                        |
| Contact carrier material      | PA 6.6                       |
| Material for screw connection | Zinc die-cast, nickel-plated |

## Connection data

### Conductor connection

|                                         |                                            |
|-----------------------------------------|--------------------------------------------|
| Connection method                       | Push-lock spring connection                |
| Connection cross section                | 0.14 mm² ... 0.5 mm² (with ferrule)        |
| Connection cross section AWG            | 26 ... 20 (with ferrule)                   |
| Stripping length of the individual wire | 7 mm                                       |
| Tightening torque                       | 0.2 Nm (M8 knurl)                          |
|                                         | 0.2 Nm (Connector with coupling sleeve)    |
|                                         | 1.5 Nm (Pressure nut with coupling sleeve) |

### Connection assignment

|                                                           |        |
|-----------------------------------------------------------|--------|
| Contact   Color (signal designation)   Contact (optional) | 1 = BN |
|                                                           | 2 = WH |
|                                                           | 3 = BU |
|                                                           | 4 = BK |

## Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 30 V AC |
|                       | 30 V DC |
| Nominal current $I_N$ | 4 A     |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Plug     |
| Head cable outlet | straight |
| Head thread type  | M8       |
| Coding            | A        |

## Cable/line

|                                         |           |
|-----------------------------------------|-----------|
| Signal type/category                    | Universal |
| Stripping length of the individual wire | 7 mm      |

## Environmental and real-life conditions

# SACC-M 8MS-4PL-M - Connector



1482520

<https://www.phoenixcontact.com/us/products/1482520>

## Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Degree of protection            | IP65                             |
|                                 | IP67                             |
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |

## Standards and regulations

### M8

|                          |                  |
|--------------------------|------------------|
| Standard designation     | M8 connector     |
| Standards/specifications | IEC 61076-2-104  |
| Standard designation     | Shock, vibration |
| Standards/specifications | EN 50155 Cat. 1B |

# SACC-M 8MS-4PL-M - Connector


1482520

<https://www.phoenixcontact.com/us/products/1482520>




## Drawings

Dimensional drawing



Functional drawing



Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

# SACC-M 8MS-4PL-M - Connector



1482520

<https://www.phoenixcontact.com/us/products/1482520>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M 8MS-4PL-M - Connector



1482520

<https://www.phoenixcontact.com/us/products/1482520>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)