

CUC-SI-CCM/RJ45-C6A - Data interface



1484215

<https://www.phoenixcontact.com/us/products/1484215>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Data interface, design: RJ45, number of positions: 8, 10 Gbps, CAT6_A (IEC 60603-7-51), material: PA, connection method: IDC connection, Ethernet



Your advantages

- Simple and tool-free mounting thanks to central fastening nut
- Space-saving installation with a standard panel cutout of Ø 22.5 mm
- Quick and easy maintenance work, updates, etc. on closed control cabinets and devices

Commercial data

Item number	1484215
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB18
Product key	ABNKAA
GTIN	4063151921392
Weight per piece (including packing)	35.77 g
Weight per piece (excluding packing)	32.865 g
Customs tariff number	85366990
Country of origin	DE

1484215

<https://www.phoenixcontact.com/us/products/1484215>

Technical data

Product properties

Product type	Data front plate
Number of positions	8
Connection profile	RJ45
Shielded	yes

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Rated surge voltage (Contact - contact)	≥ 1000 V DC
Rated surge voltage (Contact - shield)	≥ 1500 V DC
Rated current	1 A (At T = 50°C)
Contact resistance	≤ 200 mΩ (Input side to output side)
Insulation resistance	≥ 500 MΩ
Nominal voltage U _N	50 V AC
	72 V DC
Nominal current I _N	1.5 A
Contact resistance per contact pair	≤ 20 mΩ
Transmission medium	Copper
Transmission speed	10 Gbps
Transmission characteristics (category)	CAT6 _A (IEC 60603-7-51)
Power transmission	PoE++ (IEEE 802.3bt)

Connection data

Connection method	IDC connection
Tightening torque	... 1 Nm

Interfaces

Signal type/category	Ethernet CAT6 _A (IEC 60603-7-51), 10 Gbps
----------------------	--

Dimensions

Width	29.5 mm
Height	45.1 mm
Length	50.8 mm

Material specifications

Flammability rating according to UL 94 (Housing)	V0
Flammability rating according to UL 94 (Protective cover)	HB
Housing material	PA
Contact material	Copper alloy

1484215

<https://www.phoenixcontact.com/us/products/1484215>

Contact surface material	gold-plated
Contact carrier material	Die-cast zinc
Material, protective cover	TPE-V
Material for screw connection	PA

Cable/line

Signal type/category	Ethernet CAT6 _A (IEC 60603-7-51), 10 Gbps
External cable diameter	≤ 9 mm
Wire diameter (rigid)	0.41 mm ... 0.64 mm (AWG26 ... AWG22/1)
Wire diameter (flexible)	0.46 mm ... 0.76 mm (AWG27/7 ... AWG22/7)
Wire diameter including insulation	0.9 mm ... 1.6 mm

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67 (with closed protective cover)
Ambient temperature (operation)	-40 °C ... 70 °C

Mounting

Mounting type	Front mounting
Assembly note	Panel thicknesses: 1 mm ... 5 mm

CUC-SI-CCM/RJ45-C6A - Data interface



1484215

<https://www.phoenixcontact.com/us/products/1484215>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1484215>



UL Listed

Approval ID: E335024-V5S1



cUL Listed

Approval ID: E335024-V5S1

CUC-SI-CCM/RJ45-C6A - Data interface



1484215

<https://www.phoenixcontact.com/us/products/1484215>

Classifications

ECLASS

ECLASS-15.0	27440109
ECLASS-13.0	27440209

ETIM

ETIM 10.0	EC003569
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com