

VL3 PPCS12 1320 - Panel PC



1494296

<https://www.phoenixcontact.com/us/products/1494296>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP66 protected VL3 panel PC with 12" PCAP touch screen, Intel Atom® x6211E processor, 8 GB RAM, 60 GB mass storage

Similar figure

Commercial data

Item number	1494296
Packing unit	25 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBAAB
GTIN	4063151942144
Weight per piece (including packing)	5,460 g
Weight per piece (excluding packing)	4,120 g
Country of origin	TW

Technical data

Product properties

Product type	Panel PC
--------------	----------

Computer data

Processor	Intel Atom® x6211E 1.3 GHz
Trusted Platform Module	fTPM 2.0
Operating system	without operating system
RAM	8 GB LPDDR4
Data storage system	60 GB, 3D TLC
Cooling	passive
Raid system	without RAID system

Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Display formats	16:9
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	500 cd/m ²
MTBF	50,000 hours
Color spectrum	16.7 million colors
Reading angle left	88.00 °
Reading angle right	88.00 °
Reading angle top	88.00 °
Reading angle bottom	88.00 °

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Supply voltage	24 V DC ±20%
Max. current consumption	2.44 A (24 V DC)

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Connection data

Power supply

Connection method	Push-in spring connection
Conductor cross-section, rigid	0.35 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.35 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Stripping length	10 mm

VL3 PPCS12 1320 - Panel PC



1494296

<https://www.phoenixcontact.com/us/products/1494296>

Interfaces

Interfaces	2x USB 3.1 Gen. 1, Typ A 1x COM (RS-232/422/485)
Monitor output	1x DP++ 1.4
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I226-IT

Dimensions

External dimensions

Width / Height / Depth	302 mm / 229 mm / 73 mm (Outside dimensions)
------------------------	--

Installation dimensions

Width / Height / Installation depth	292 mm / 219 mm / (Installation cutout)
-------------------------------------	---

Material specifications

Color (Housing)	light gray (RAL 7035)
Material front plate	Aluminum (natural anodized)
Housing material	Sheet steel

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (front (panel mount)) IP30 (back/all around when VESA installed)
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock	15g with 11 ms impulse
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
UL, USA / Canada	UL 61010-1, UL 61010-2-201 Class I, Div. 2, Groups A, B, C, D T4

Mounting

Mounting type	Panel cutout VESA holder
Holder system	VESA MIS-D 100 C

VL3 PPCS12 1320 - Panel PC

1494296

<https://www.phoenixcontact.com/us/products/1494296>



Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1494296>



IECEE CB Scheme

Approval ID: US-44890-UL



cULus Listed

Approval ID: E196811 V13S3

VL3 PPCS12 1320 - Panel PC



1494296

<https://www.phoenixcontact.com/us/products/1494296>

Classifications

ECLASS

ECLASS-13.0	19200103
ECLASS-15.0	19200103

ETIM

ETIM 10.0	EC001414
-----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------