

# CBL-SEB-14P-V-CE/UL-SL - Secure Edge Box



1495004

<https://www.phoenixcontact.com/us/products/1495004>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular switchgear and controlgear assembly for production networks, with firewall function for secure network segmentation, local data storage, web visualization, and cloud connection, with sheet-steel housing. Machine learning integration per PLCnext App possible.

The figure shows item version  
1473591 with stainless steel housing

## Product description

The switchgear and controlgear assembly Secure Edge Box (SEB) is used as a secure interface between the production network and higher-level IT networks, external service providers, or cloud systems.

The Secure Edge Box segments the production network. Segmentation improves network security and enables authorized external VPN access.

Unauthorized access is blocked by the firewall of the integrated mGuard router. The firewall allows only the necessary data traffic in order to optimally protect the segmented network.

VPN access can be enabled with a switch in the housing door. Optionally, VPN access is also possible via the mGuard Secure Cloud.

Active VPN connections are visualized by a signal light on top of the housing. The door contact provides additional tamper protection by sending a message to the control system when the door is opened.

The Secure Edge Box is optimized for use with the switchgear and controlgear assembly Data Collection Box (see "Accessories"). The integrated edge PC enables data acquisition of connected sensors of the Data Collection Box (e.g., energy measuring devices, flow meters) as well as further process data. The data is saved and visualized locally. Data can be passed to higher-level systems as well as established cloud systems.

## IMPORTANT NOTE:

For the function extension of the Secure Edge Box you require additional application software. You can purchase and download the corresponding license in the PLCnext Store (<https://www.plcnextstore.com>).

License overview:

- IIoT framework
- InfluxDB for PLCnext x86
- Grafana for PLCnext x86
- NodeRED for PLCnext x86
- MLnext Execution

## Your advantages

- Fast installation and startup
- Simple firewall handling with locally controllable VPN access and signal light
- Offline data storage and visualization possible
- Data forwarding to different cloud systems possible
- Tamper protection via door switch

# CBL-SEB-14P-V-CE/UL-SL - Secure Edge Box



1495004

<https://www.phoenixcontact.com/us/products/1495004>

## Commercial data

Item number	1495004
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DTHDAA
GTIN	4063151943455
Weight per piece (including packing)	53 kg
Weight per piece (excluding packing)	53 kg
Country of origin	DE

1495004

<https://www.phoenixcontact.com/us/products/1495004>

## Technical data

### Product properties

Product type	Switchgear and controlgear assembly
--------------	-------------------------------------

### Insulation characteristics

Protection class	I
------------------	---

### Electrical properties

Supply voltage range	85 V AC ... 264 V AC (50/60 Hz)
Nominal current $I_N$	1.66 A (100 V AC)
	0.94 A (240 V AC)
Nominal power	208 VA

### Fuse

Recommended backup fuse:	16 A
--------------------------	------

### Connection data

#### AC supply voltage

Type of cable entry	Cable gland (M20)
Cable cross-section range: Without ferrule	0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup> (rigid/flexible)
Cable cross-section range: With ferrule	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (flexible)
External cable diameter	6 mm ... 12 mm

#### Communication

Type of cable entry	CES cable feed-through
External cable diameter	2x 6 mm ... 7 mm

### Interfaces

#### Ethernet

Bus system	RJ45
Number of interfaces	14 (can be extended to max. 50)
Connection method	RJ45 jack
Transmission speed	10/100 Mbps
Transmission length	max. 100 m (per segment)

### Dimensions

#### External dimensions

Width / Height / Depth	600 mm / 800 mm / 300 mm (Housing dimensions without attachment parts)
------------------------	--

### Material specifications

Material	Sheet steel
----------	-------------

1495004

<https://www.phoenixcontact.com/us/products/1495004>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP54
	NEMA 1
Ambient temperature (operation)	0 °C ... 40 °C
Permissible humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Air pressure (operation)	70 kPa ... 106 kPa

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### UL, USA/Canada

Identification	UL 508A
	CSA C22.2 No. 14-2005

# CBL-SEB-14P-V-CE/UL-SL - Secure Edge Box



1495004

<https://www.phoenixcontact.com/us/products/1495004>

## Classifications

### ECLASS

ECLASS-13.0	27370190
ECLASS-15.0	27370190

### ETIM

ETIM 9.0	EC012357
----------	----------

# CBL-SEB-14P-V-CE/UL-SL - Secure Edge Box



1495004

<https://www.phoenixcontact.com/us/products/1495004>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)