

# SAC-4P-...-PVC TP - Cable reel



1500321

<https://www.phoenixcontact.com/us/products/1500321>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Loop 2 M12 cable (PVC), green, 2 x 2 x 0.5 mm<sup>2</sup>, twisted pair, by the meter

## Commercial data

Item number	1500321
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF1CCA
Customs tariff number	85445980
Country of origin	DE

# SAC-4P-...-PVC TP - Cable reel



1500321

<https://www.phoenixcontact.com/us/products/1500321>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	4
Shielded	no

### Material specifications

Outer sheath, material	PVC
Conductor material	Bare Cu litz wires

### Cable/line

Cable type	PVC, green
Cable abbreviation	LiYY
External cable diameter	8.10 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6017
Single wire, color	brown, white, green, yellow
Cable cross section	0.5 mm <sup>2</sup>
Conductor material	Bare Cu litz wires
Conductor structure signal line	16x 0.20 mm
AWG signal line	20
Material wire insulation	PVC
Overall twist	Wires twisted in pair
Nominal voltage, cable	300 V
Test voltage, cable	1500 V

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

# SAC-4P-...-PVC TP - Cable reel



1500321

<https://www.phoenixcontact.com/us/products/1500321>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)