

SACC-DSIP-M12FSB-5CON-L180-SI - Device connector rear mounting



1528251

<https://www.phoenixcontact.com/us/products/1528251>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Universal, 5-position, Socket, straight, M12, B-coding, Wave soldering

Commercial data

Item number	1528251
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB26
Product key	ABQEQA
GTIN	4046356023238
Weight per piece (including packing)	24 g
Weight per piece (excluding packing)	15.911 g
Customs tariff number	85366990
Country of origin	DE

SACC-DSIP-M12FSB-5CON-L180-SI - Device connector rear mounting



1528251

<https://www.phoenixcontact.com/us/products/1528251>

Technical data

Mounting

Mounting type	Rear mounting
---------------	---------------

Product properties

Product type	Circular connectors (device side)
Sensor type	Universal
Number of positions	5
Shielded	no
Coding	B
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Insulating body	PBT
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	V0

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	60 V
Contact resistance	$\leq 0.003 \Omega$
Insulation resistance	$\geq 1 T\Omega$
Nominal voltage U_N	60 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
Head cable outlet	straight

SACC-DSIP-M12FSB-5CON-L180-SI - Device connector rear mounting



1528251

<https://www.phoenixcontact.com/us/products/1528251>

Head thread type	M12
Coding	B

Cable/line

Signal type/category	Universal
----------------------	-----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
UL Type Rating	Type 4 (indoor use only)

SACC-DSIP-M12FSB-5CON-L180-SI - Device connector rear mounting




1528251

<https://www.phoenixcontact.com/us/products/1528251>

Drawings

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

SACC-DSIP-M12FSB-5CON-L180-SI - Device connector rear mounting



1528251

<https://www.phoenixcontact.com/us/products/1528251>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSIP-M12FSB-5CON-L180-SI - Device connector rear mounting



1528251

<https://www.phoenixcontact.com/us/products/1528251>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7e06980c-21ce-43e0-846c-79bbd2563675

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com