# SACC-E-M5FS-3CON-M5/0,5 - Device connector front mounting

1530605

https://www.phoenixcontact.com/us/products/1530605

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, 3-position, Socket, straight, M5, A-coding, on free cable end, Individual wires, cable length: 0.5 m, 0.14 $mm^2$, TPE litz wire

## Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness

## Commercial data

| | |
|---|---|
| Item number | 1530605 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB21 |
| Product key | ABQMBA |
| GTIN | 4046356024402 |
| Weight per piece (including packing) | 6.8 g |
| Weight per piece (excluding packing) | 6.8 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

## Technical data

### Mounting

| | |
|---|---|
| Mounting type | Front mounting (M5 x 0,5) |

### Product properties

| | |
|---|---|
| Product type | Circular connectors (device side) |
| Application | Signal |
| Number of positions | 3 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |
| Thread type | M5 |

Insulation characteristics

| | |
|---|---|
| Overvoltage category | II |
| Degree of pollution | 3 |

### Material specifications

| | |
|---|---|
| Flammability rating according to UL 94 | HB |
| Material grommet GRP | Viton |
| Contact material | CuSn |
| Contact surface material | Au |
| Contact carrier material | PA 6.6 |
| Material for screw connection | Brass, nickel-plated |

### Electrical properties

| | |
|---|---|
| Contact resistance | ≤ 3 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage $U_N$ | 48 V AC |
| | 60 V DC |
| Nominal current $I_N$ | 1 A |
| Test voltage | 800 V |

### Connection data

Conductor connection

| | |
|---|---|
| Connection method | Individual wires |
| Contact connection type | Socket |
| Conductor cross-section | 0.14 mm² |

### Connector

Connection 1

| | |
|---|---|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M5 |
| Coding | A |

Connection 2

| | |
|---|---|
| Head design | free cable end |

## Cable/line

| | |
|---|---|
| Cable length | 0.5 m |
| Cable type | TPE litz wire |
| Single wire, color | brown, blue, black |
| Cable cross section | 0.14 mm² |
| Conductor structure signal line | 18x 0.10 mm |
| AWG signal line | 26 |
| Material wire insulation | TPE |
| Ambient temperature (operation) | -25 °C ... 80 °C (cable, fixed installation) |

## Environmental and real-life conditions

Ambient conditions


| | |
|---|---|
| Degree of protection | IP67 |
| Ambient temperature (operation) (Cable, fixed installation) | -25 °C ... 80 °C (cable, fixed installation) |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 85 °C (Plug) |

## Standards and regulations

| | |
|---|---|
| Standard designation | M5 connector |
| Standards/specifications | according to IEC 61076-2-105 |

## Drawings

Schematic diagram




Pin assignment M5 socket, 3-pos., D-coded, view female side

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440103 |
| ECLASS-15.0 | 27440103 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC003570 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | d36c1cfc-e9e0-4983-9ece-5e6142d122fe |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 1.395 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com