

# SACC-E-M5FS-4CON-M5/0,5 - Device connector front mounting



1530618

<https://www.phoenixcontact.com/us/products/1530618>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, 4-position, Socket, straight, M5, A-coding, on free cable end, Individual wires, cable length: 0.5 m, 0.14 mm<sup>2</sup>, TPE litz wire

## Your advantages

- Preassembled with litz wires for immediate use
- Customer-specific assemblies and litz wire lengths available
- Sealed on the litz wire side for optimum leak-tightness

## Commercial data

Item number	1530618
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB21
Product key	ABQMBA
GTIN	4046356024419
Weight per piece (including packing)	8 g
Weight per piece (excluding packing)	8 g
Customs tariff number	85444290
Country of origin	DE

# SACC-E-M5FS-4CON-M5/0,5 - Device connector front mounting



1530618

<https://www.phoenixcontact.com/us/products/1530618>

## Technical data

### Mounting

Mounting type	Front mounting (M5 x 0,5)
---------------	---------------------------

### Product properties

Product type	Circular connectors (device side)
Application	Signal
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A
Thread type	M5

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Seal material	Viton
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Brass, nickel-plated

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	1 A
Test voltage	800 V

### Connection data

#### Conductor connection

Connection method	Individual wires
Contact connection type	Socket
Conductor cross-section	0.14 mm <sup>2</sup>

### Connector

#### Connection 1

# SACC-E-M5FS-4CON-M5/0,5 - Device connector front mounting



1530618

<https://www.phoenixcontact.com/us/products/1530618>

Head design	Socket
Head cable outlet	straight
Head thread type	M5
Coding	A

## Connection 2

Head design	free cable end
-------------	----------------

## Cable/line

Cable length	0.5 m
Cable type	TPE litz wire
Single wire, color	brown, white, blue, black
Cable cross section	0.14 mm <sup>2</sup>
Conductor structure signal line	18x 0.10 mm
AWG signal line	26
Material wire insulation	TPE
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (Cable, fixed installation)	-25 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug)

## Standards and regulations

Standard designation	M5 connector
Standards/specifications	according to IEC 61076-2-105


# SACC-E-M5FS-4CON-M5/0,5 - Device connector front mounting

1530618

<https://www.phoenixcontact.com/us/products/1530618>

## Drawings

Schematic diagram



Pin assignment M5 socket, 4-pos., D-coded, view female side

# SACC-E-M5FS-4CON-M5/0,5 - Device connector front mounting



1530618

<https://www.phoenixcontact.com/us/products/1530618>

## Classifications

### ECLASS

ECLASS-13.0	27440103
ECLASS-15.0	27440103

### ETIM

ETIM 10.0	EC003570
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-E-M5FS-4CON-M5/0,5 - Device connector front mounting



1530618

<https://www.phoenixcontact.com/us/products/1530618>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5f8f1330-1b40-48e4-a4f2-47c6cdad8432

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)