

SAC-4P-100,0-180/0,25 - Cable reel



1501812

<https://www.phoenixcontact.com/us/products/1501812>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

By the meter, Cable reel, PUR halogen-free, orange RAL 2003, 4-wire, color single wire: brown, white, blue, black, cable length: 100 m



Commercial data

Item number	1501812
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LBA
GTIN	4017918813949
Weight per piece (including packing)	3.47 g
Weight per piece (excluding packing)	3.47 g
Customs tariff number	85444995
Country of origin	DE

SAC-4P-100,0-180/0,25 - Cable reel

1501812

<https://www.phoenixcontact.com/us/products/1501812>

Technical data


Product properties

Product type	Cable by the meter
Number of positions	4

Cable/line

Cable length	100 m
--------------	-------

PUR halogen-free orange [180]

Dimensional drawing	
Cable weight	25 kg/km
UL AWM Style	20549
Number of positions	4
Shielded	no
Cable type	PUR halogen-free orange [180]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	4x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm (Signal line)
External cable diameter	4.40 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) 0.75 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 10 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	22 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.

SAC-4P-100,0-180/0,25 - Cable reel



1501812

<https://www.phoenixcontact.com/us/products/1501812>

Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with DIN UL-Style 20549
Ambient temperature (operation)	-25 °C ... 80 °C (Cable)

SAC-4P-100,0-180/0,25 - Cable reel



1501812

<https://www.phoenixcontact.com/us/products/1501812>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

SAC-4P-100,0-180/0,25 - Cable reel



1501812

<https://www.phoenixcontact.com/us/products/1501812>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com