

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor



1534480

<https://www.phoenixcontact.com/us/products/1534480>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Non-contact safety switch, sensor, up to Cat. 4, PL e (EN ISO 13849), SIL 3 (EN IEC 62061), design 4 (EN ISO 14119), low encoding level, 2 N/O contacts, compact design, 5 m open PVC cable

## Product description

The PSR-MIS non-contact safety switches offer a cost-optimized safety solution. The safety switches in this series use the proven magnetic switching principle for monitoring of movable guards and are easy to install.

## Your advantages

- Cost-optimized safety switch
- Tried-and-tested magnetic switching principle
- Compact design
- Can be used with standard actuators
- Flexible connection, due to open cable end
- Spacer plates for mounting on ferrous material available as accessories

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1534480       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN04          |
| Product key                          | DNA642        |
| GTIN                                 | 4067923005679 |
| Weight per piece (including packing) | 170 g         |
| Weight per piece (excluding packing) | 155 g         |
| Customs tariff number                | 85365019      |
| Country of origin                    | DE            |

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor



1534480

<https://www.phoenixcontact.com/us/products/1534480>

## Technical data

### Product properties

|                                                |                        |
|------------------------------------------------|------------------------|
| Product type                                   | Safety switches        |
| Product family                                 | PSR-MIS                |
| Technology                                     | Magnetic               |
| Application                                    | Safety door monitoring |
|                                                | Position monitoring    |
| Design in accordance with EN ISO 14119         | 4                      |
| Encoding level in accordance with EN ISO 14119 | low                    |

### Insulation characteristics

|                  |   |
|------------------|---|
| Pollution degree | 3 |
|------------------|---|

### Times

|               |      |
|---------------|------|
| Response time | 1 ms |
|---------------|------|

### Switching intervals (Actuation position frontal)

|                   |                                                                                            |
|-------------------|--------------------------------------------------------------------------------------------|
| Actuation setting | 1 (frontal), see the "Actuation positions and travel directions" section in the data sheet |
|-------------------|--------------------------------------------------------------------------------------------|

## Electrical properties

### Sensor

|                                 |                            |
|---------------------------------|----------------------------|
| Contact switching type          | 2 N/O contacts             |
| Utilization category            | DC12                       |
| Rated insulation voltage $U_i$  | max. 75 V DC               |
|                                 | max. 50 V AC               |
| Voltage                         | min. 0 V DC (SELV/PELV)    |
|                                 | max. 28.8 V DC (SELV/PELV) |
| Current                         | min. 0 mA                  |
|                                 | max. 100 mA                |
| Rated impulse withstand voltage | 0.8 kV ( $U_{imp}$ )       |
| Switching frequency             | max. 5 Hz                  |
| Resistance                      | 22 $\Omega$                |
| Cable length                    | max. 30 m                  |

## Connection data

### Conductor connection

|                                          |                                     |
|------------------------------------------|-------------------------------------|
| Connection method                        | open cable end                      |
| Note regarding the connection technology | 5 m PVC cable, tin-plated cable end |

## Dimensions


|                |     |
|----------------|-----|
| Length (Cable) | 5 m |
|----------------|-----|

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor



1534480

<https://www.phoenixcontact.com/us/products/1534480>

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 36 mm                                                                              |
| Height              | 26 mm                                                                              |
| Depth               | 13 mm                                                                              |

## Material specifications

|                  |                           |
|------------------|---------------------------|
| Color (Housing)  | traffic yellow (RAL 1023) |
| Housing material | PBT                       |

## Characteristics

Safety data: EN ISO 13849-1

|                        |   |
|------------------------|---|
| Performance level (PL) | e |
|------------------------|---|

Safety data

|                              |   |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

## Environmental and real-life conditions

Ambient conditions

|                                         |                            |
|-----------------------------------------|----------------------------|
| Degree of protection                    | IP67                       |
| Ambient temperature (operation)         | -25 °C ... 75 °C           |
| Ambient temperature (storage/transport) | -25 °C ... 75 °C           |
| Maximum altitude                        | ≤ 2000 m (Above sea level) |
| Shock                                   | 30g, 11 ms                 |
| Vibration (operation)                   | 10 Hz ... 55 Hz            |

## Mounting

|                   |                                                               |
|-------------------|---------------------------------------------------------------|
| Mounting type     | not flush                                                     |
| Assembly note     | Note EN ISO 14119<br>max. tightening torque to secure: 2.9 Nm |
| Mounting position | any, sensor and actuator parallel to each other               |
| Minimum distance  | min. 50 mm (between two safety switching systems)             |

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor




1534480

<https://www.phoenixcontact.com/us/products/1534480>


## Drawings

Dimensional drawing



Dimensions (in mm)

Circuit diagram



Circuit diagram

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor



1534480

<https://www.phoenixcontact.com/us/products/1534480>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1534480>



**ETLus**

Approval ID: Industrial Component



**cETL**

Approval ID: Industrial component



**Functional Safety**

Approval ID: Z10029429 0060 Rev01

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor



1534480

<https://www.phoenixcontact.com/us/products/1534480>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27274401 |
| ECLASS-15.0 | 27274401 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002544 |
|-----------|----------|

# PSR-MIS-RS-S-NONO-C-5,0PVC - Safety switch sensor



1534480

<https://www.phoenixcontact.com/us/products/1534480>

## Environmental product compliance

### EU RoHS

|                                         |        |
|-----------------------------------------|--------|
| Fulfills EU RoHS substance requirements | Yes    |
| Exemption                               | 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-25                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)