

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting



1534627

<https://www.phoenixcontact.com/us/products/1534627>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bus system flush-type socket, Ethernet, 4-pos., M12, shielded, D-coded, rear/screw mounting, with straight solder connection

## Your advantages

- Standard pin assignments and codings for signal transmission with a uniform design-in design

## Commercial data

Item number	1534627
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB23
Product key	ABQEHI
GTIN	4046356026796
Weight per piece (including packing)	14.79 g
Weight per piece (excluding packing)	14.51 g
Customs tariff number	85366990
Country of origin	HU

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting



1534627

<https://www.phoenixcontact.com/us/products/1534627>

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Mounting

Mounting type	Rear mounting (M12 x 1, with locking nut)
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

### Product properties

Product type	Circular connectors (device side)
Application	Data
	Signal
Number of positions	4
Shielded	yes
Coding	D
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

### Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	250 V
Nominal current $I_N$	4 A

### Connection data

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting



1534627

<https://www.phoenixcontact.com/us/products/1534627>

## Conductor connection

Connection method	Wave soldering
Contact connection type	Socket
Tightening torque	1 Nm ... 1.5 Nm (Installation-side)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Connector

### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	D

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C -40 °C ... 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting

1534627

<https://www.phoenixcontact.com/us/products/1534627>

## Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting





1534627


<https://www.phoenixcontact.com/us/products/1534627>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1534627>

 <b>cUL Recognized</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	250 V	4 A	-	-

 <b>UL Recognized</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	250 V	4 A	-	-

 <b>UL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	250 V	4 A	-	-

 <b>cUL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	250 V	4 A	-	-

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting



1534627

<https://www.phoenixcontact.com/us/products/1534627>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-M12FSD-4CON-L180 - Device connector rear mounting



1534627

<https://www.phoenixcontact.com/us/products/1534627>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f785135d-8075-4150-8f3f-5b5a35a3b3ce

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)