

SAC-5P-M12MS CAN 150 TR - Termination resistor



1536162

<https://www.phoenixcontact.com/us/products/1536162>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminating resistor CANopen®/DeviceNet™ M12



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1536162 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF10 |
| Product key | AF1GVX |
| GTIN | 4046356027540 |
| Weight per piece (including packing) | 11.91 g |
| Weight per piece (excluding packing) | 8.11 g |
| Customs tariff number | 85332100 |
| Country of origin | DE |

SAC-5P-M12MS CAN 150 TR - Termination resistor



1536162

<https://www.phoenixcontact.com/us/products/1536162>

Technical data

Product properties

| | |
|---------------------|-------------------|
| Product type | Terminal resistor |
| Number of positions | 5 |
| Coding | A |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------|--------------------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |
| | 5 V _{rms} |
| Nominal current I_N | 4 A |

General

| | |
|----------------------|--------------------------------|
| Termination resistor | 150 Ω (Contact 2 and 4) |
|----------------------|--------------------------------|

Signaling

| | |
|------------------------|----|
| Status display | no |
| Status display present | no |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | HB |
| Material of grip body | TPU, hardly inflammable, self-extinguishing |
| Contact material | CuSn |
| Contact surface material | Ni/Au |
| Contact carrier material | TPU GF |
| Material for screw connection | Zinc die-cast, nickel-plated |

Connector

Connection 1

| | |
|---------------------|-------------------|
| Type | Plug straight M12 |
| Number of positions | 5 |
| Coding type | A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|------------|

Environmental and real-life conditions

SAC-5P-M12MS CAN 150 TR - Termination resistor



1536162

<https://www.phoenixcontact.com/us/products/1536162>

Ambient conditions

| | |
|---|-------------------------|
| Degree of protection | IP65 |
| | IP67 |
| | IP68 |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug) |

Standards and regulations

M12

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |


SAC-5P-M12MS CAN 150 TR - Termination resistor

1536162

<https://www.phoenixcontact.com/us/products/1536162>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side


SAC-5P-M12MS CAN 150 TR - Termination resistor



1536162

<https://www.phoenixcontact.com/us/products/1536162>

Circuit diagram



Internal wiring of connections

SAC-5P-M12MS CAN 150 TR - Termination resistor



1536162

<https://www.phoenixcontact.com/us/products/1536162>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19070403 |
| ECLASS-15.0 | 19070403 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000448 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32121600 |
|-------------|----------|

SAC-5P-M12MS CAN 150 TR - Termination resistor



1536162

<https://www.phoenixcontact.com/us/products/1536162>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.272 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com