

SAC-3P-M 8FR/100/5,0 GY IN - Sensor/actuator cable



1536874

<https://www.phoenixcontact.com/us/products/1536874>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, PUR/PVC, gray RAL 7001, free cable end, on Socket angled M8, coding: A, cable length: 5 m

Commercial data

Item number	1536874
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	AF1BBA
GTIN	4046356073370
Weight per piece (including packing)	137.4 g
Weight per piece (excluding packing)	117.4 g
Country of origin	DE

SAC-3P-M 8FR/100/5,0 GY IN - Sensor/actuator cable



1536874

<https://www.phoenixcontact.com/us/products/1536874>

Technical data

Product properties

Product type	Sensor/actuator cable
Shielded	no
Coding	A

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Connector

Connection 1

Type	free cable end
------	----------------


Connection 2

Type	Socket angled M8
Coding type	A

Cable/line

Cable length	5 m
--------------	-----

PUR/PVC gray [100]

Dimensional drawing	
Cable weight	27 kg/km
Number of positions	3
Shielded	no
Cable type	PUR/PVC gray [100]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	0.25 mm ²
Wire diameter incl. insulation	1.32 mm ±0.02 mm
External cable diameter	4.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PVC

SAC-3P-M 8FR/100/5,0 GY IN - Sensor/actuator cable



1536874

<https://www.phoenixcontact.com/us/products/1536874>

Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
	≥ 0.38 mm (Outer cable sheath)
	approx. 3.50 mm ±0.1 mm (Inner sheath)
Overall twist	3 wires, twisted
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	22 mm
Smallest bending radius, movable installation	44 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 44 mm, Traversing path: 5 m, Traversing rate: 3 m/s
Flame resistance	As per UL-Style 2464
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-3P-M 8FR/100/5,0 GY IN - Sensor/actuator cable



1536874

<https://www.phoenixcontact.com/us/products/1536874>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

SAC-3P-M 8FR/100/5,0 GY IN - Sensor/actuator cable



1536874

<https://www.phoenixcontact.com/us/products/1536874>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com