

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable



1538814

<https://www.phoenixcontact.com/us/products/1538814>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12 SPEEDCON, coding: A, on Socket straight M8, cable length: 0.6 m

## Commercial data

Item number	1538814
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF1BBA
GTIN	4046356077453
Weight per piece (including packing)	27.7 g
Weight per piece (excluding packing)	27.7 g
Country of origin	PL

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable



1538814

<https://www.phoenixcontact.com/us/products/1538814>

## Technical data

### Product properties

Product type	Sensor/actuator cable
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

### Material specifications

Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated
Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC
Nominal current $I_N$	4 A
Max. conductor resistance	77.6 $\Omega/m$

### Mechanical properties

#### Mechanical data

Max. bending cycles	4000000
---------------------	---------

### Signaling

Status display present	no
------------------------	----

### Connector

#### Connection 1

Type	Plug straight M12 SPEEDCON
Number of positions	3
Locking type	SPEEDCON
Coding type	A

#### Connection 2


Type	Socket straight M8
Number of positions	3

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable

1538814

<https://www.phoenixcontact.com/us/products/1538814>

## Cable/line

Cable length	0.6 m
PUR halogen-free black [PUR]	
Dimensional drawing	
Cable weight	18 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross-section	3x 0.25 mm <sup>2</sup> (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm
External cable diameter	3.60 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation)
Thickness, outer sheath	approx. 0.50 mm
Overall twist	3 wires, twisted
Length of twist, overall twist	40 mm
Max. conductor resistance	≤ 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	18 mm
Smallest bending radius, movable installation	36 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 44 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable



1538814

<https://www.phoenixcontact.com/us/products/1538814>

	DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	hydrolysis and microbe resistant
	Highly resistant to acids, alkaline solutions and solvents
	Resistant to salt water
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable

1538814

<https://www.phoenixcontact.com/us/products/1538814>

## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Dimensional drawing



Socket M8 x 1, straight

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable

1538814

<https://www.phoenixcontact.com/us/products/1538814>

Schematic diagram



Pin assignment M12 plug, 3-pos., A-coded, view male side

Schematic diagram



Pin assignment M8 socket, 3-pos.

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable



1538814

<https://www.phoenixcontact.com/us/products/1538814>

Circuit diagram



Contact assignment of M12 plugs / M8 sockets

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable



1538814

<https://www.phoenixcontact.com/us/products/1538814>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-3P-MS/ 0,6-170/M 8FS SCO - Sensor/actuator cable



1538814

<https://www.phoenixcontact.com/us/products/1538814>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)