

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051
<https://www.phoenixcontact.com/us/products/1511051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, PUR halogen-free, black-gray RAL 7021, Plug straight M12, coding: A, on free cable end, cable length: 5.5 m

Commercial data

Item number	1511051
Packing unit	5 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4017918903091
Weight per piece (including packing)	213.52 g
Weight per piece (excluding packing)	208.14 g
Country of origin	PL

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051

<https://www.phoenixcontact.com/us/products/1511051>

Technical data

Product properties

Product type	Sensor/actuator cable
Shielded	no
Coding	A

Material specifications

Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Max. conductor resistance	58 Ω /km

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
Max. bending cycles	4000000

Connector

Connection 1

Type	Plug straight M12
Coding type	A

Connection 2


Type	free cable end
------	----------------

Cable/line

Cable length	5.5 m
--------------	-------

PUR, black, 5th conductor gray [115]

Dimensional drawing



Cable weight	35 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	5

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051

<https://www.phoenixcontact.com/us/products/1511051>

Shielded	no
Cable type	PUR, black, 5th conductor gray [115]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	5x 0.34 mm ²
Wire diameter incl. insulation	1.27 mm ±0.02 mm
External cable diameter	5.00 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material, filler	PP
Material wire insulation	PP
Single wire, color	brown, white, blue, black, gray
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.70 mm
Overall twist	5 cores, twisted
Max. conductor resistance	≤ 58 Ω/km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	25 mm
Smallest bending radius, movable installation	50 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 50 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥5000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with DIN UL-Style 20549 in accordance with UL 758/1581 FT2
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A) hydrolysis and microbe resistant Resistant to salt water Low adhesion abrasion-resistant
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051
<https://www.phoenixcontact.com/us/products/1511051>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051

<https://www.phoenixcontact.com/us/products/1511051>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1511051>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051

<https://www.phoenixcontact.com/us/products/1511051>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MS/5,5-115 SO V2A - Sensor/actuator cable



1511051

<https://www.phoenixcontact.com/us/products/1511051>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.602 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com