

# SACB-16X0,5/3X1,0-50 PUR SH - Master cable ring



1539156

<https://www.phoenixcontact.com/us/products/1539156>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Master cable ring, application: Distributor boxes, number of positions: 19, shielding: yes



## Commercial data

Item number	1539156
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF45
Product key	AF3ZBX
GTIN	4046356076357
Weight per piece (including packing)	11,586 g
Weight per piece (excluding packing)	11,586 g
Customs tariff number	85444290
Country of origin	DE

# SACB-16X0,5/3X1,0-50 PUR SH - Master cable ring

1539156

<https://www.phoenixcontact.com/us/products/1539156>

## Technical data

### Product properties


Product type	Cable by the meter
Application	Distributor boxes
Number of positions	19
LED	no

### Electrical properties

Nominal voltage $U_N$	300 V AC
	300 V DC

### Cable/line

PUR/PVC shielded, black [PUR]

Dimensional drawing	
Number of positions	19
Shielded	yes
Cable type	PUR/PVC shielded, black [PUR]
Conductor structure signal line	64x 0.10 mm
AWG signal line	20
Conductor structure, voltage supply	128x 0.10 mm
AWG power supply	17
Conductor cross-section	16x 0.5 mm <sup>2</sup> (Signal line)
	3x 1 mm <sup>2</sup> (Power supply)
Wire diameter incl. insulation	1.6 mm (Signal line)
	2 mm (power line)
External cable diameter	11.60 mm ±0.3 mm
Outer sheath, material	PUR
External sheath, color	deep black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet, gray/pink, red/blue, white/green, brown/green, white/yellow, yellow/brown, white/gray, gray/brown
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V

# SACB-16X0,5/3X1,0-50 PUR SH - Master cable ring



1539156

<https://www.phoenixcontact.com/us/products/1539156>

Test voltage	2000 V
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 10 x D, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

# SACB-16X0,5/3X1,0-50 PUR SH - Master cable ring



1539156

<https://www.phoenixcontact.com/us/products/1539156>

## Classifications

### ECLASS

ECLASS-13.0	27060106
ECLASS-15.0	27060106

### ETIM

ETIM 10.0	EC003250
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SACB-16X0,5/3X1,0-50 PUR SH - Master cable ring



1539156

<https://www.phoenixcontact.com/us/products/1539156>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	41.56 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)